

IC Housings

Ilco IC Housings are machined from solid brass bar stock, engineered and manufactured to OEM specifications.

R2800 Series - Small Format IC Core Convertible Housing

- 6 finishes - 03, 04, 10, 10B, 26D, 26
- Interchangeable cams provide flexibility
- Small and Large format mortise housings utilize the same cams
- Thin Head Mortise Style converts to Rim using the R2800 kit (sold separately)
- Available in Tapered Head Mortise Style
- Compatible with manufacturers of all small format Best® size cores



R28106	Thin Head Mortise, 1 1/4", (31.7mm), 6 Pin
R28107	Thin Head Mortise, 1 3/8", (34.9mm), 6 & 7 Pin
R28507	Thin Head Mortise, 1 1/2", (38.1mm), 6 & 7 Pin
R28607	Thin Head Mortise, 1 5/8" (41.2mm), 6 & 7 Pin
R28206	Thin Head Rim , 1 1/4", (31.7mm), 6 Pin
R28207	Thin Head Rim , 1 3/8", (34.9mm), 6 & 7 Pin
R28406	Tapered Head Mortise, 15/16", (23.8mm), 6 Pin
R28407	Tapered Head Mortise, 1", (25.4mm), 6 & 7 Pin

S2600 Series - Large Format IC Core Convertible Housing - Schlage® Size

- 4 finishes - 03, 10B, 26D, 26
- Length: 1 1/2" (38.1mm)
- Interchangeable cams provide flexibility
- Small and Large format mortise housings utilize the same cams
- Accept Schlage® size large format interchangeable cores
- Mortise style converts to Rim using the S2600 kit (sold separately).

S26506	Mortise
S26206	Rim



Ilco®