



SUPPLYING THE GLOBAL SECURITY COMMUNITY SINCE 1956

Universal Pinning Kits

Only LAB kits contain the most up-to-date, comprehensive pinning charts with technical data straight from the manufacturers. LAB's exclusive "eye saver" exploded view of information helps make pinning easy and accurate.

Woody Classic

LWK003

104 sizes
Top/Master Pin sizes: .024 - .170
Bottom Sizes: .165 - .360
Springs 115L/115S
72 Pins per pocket

LWK005

92 sizes
Top/Master Pin sizes: .010 - .250
Bottom Sizes: .150 - .360
Springs 115L/115S
72 Pins per pocket

Features

Beautifully handcrafted in maple by New England wood craftsmen. Protected in clear polyfinish to preserve its outstanding qualities.

- **New** larger printing under pin pockets
- **New** larger "finger pin pockets"
- Color Passport Pin Chart®
- Triple-latch protection
- Slide-out center drawer with Master Pins, Springs and Tool compartment



15 3/4" x 8 1/4" x 3"



SMART WEDGE



Exclusive Features

- Developed by locksmiths with confined workspace in mind.
- Color Passport Pinning Chart with up-to-date factory pinning data
- Slide-out tool drawer
- 3 deep spring pockets
- .115 Long - **NEW** Tangle Resistant Springs
- .115 Short - Short Springs
- T-Pin Spring for Schlage® "F" Series Cylinders
- Double-sized pin pockets (holds up to 200 pins per size)
- Large tool pocket on top of tray
- Injected Molded High-Impact Tray with pin sizes printed 100% larger
- Contains 3 sizes of spool pins and the "F" Series T-Pin for Schlage® Cylinders
- 72 Pins per pocket • 100 Springs per pocket



LSW003

Pin Sizes:
• .003 Increments
• 92 Sizes
• Top Pins: .024 - .200, .235
• Spool Pins: .160, .165, .180
• T-Pin: .170
• Bottom Pins: .159 - .354*

LSW005

Pin Sizes:
• .005 Increments
• 86 Sizes
• Top Pins: .010 - .200, .230, .235
• Spool Pins: .160, .165, .180
• T-Pin: .170
• Bottom Pins: .155 - .360

* Contains the most commonly used sizes - No Dead Stock

FOR MORE DETAILS SEE WEBSITE www.labpins.com

Drawer Size: 6 1/2" Long
5 1/2" Wide
1- 1 7/8" Drawer side-angled

Size: 13 1/4" X 10 1/2" 2" F X 3 1/4" B