


Butterfly Valve Lockout Devices

Locks out virtually all butterfly valves

- ▶ Easy-to-use, adjustable design fits virtually all butterfly valves
- ▶ Locks out valve in seconds by feeding S806 cable lockout device through desired eyelet and around valve neck
- ▶ Stainless steel rivet allows device to smoothly pivot open and closed to ensure proper fit
- ▶ Durable, lightweight Xenex™ Thermoplastic material is chemical resistant and performs effectively in extreme environments
- ▶ Directional application arrows allow for ease of installation and minimize user error

Master Lock Model #	Description
S3920	Butterfly Valve Lockout Device only
S3921	Butterfly Valve Lockout Device + S806CBL3 Adjustable cable lockout



Valve Lockouts

The exclusive, patented Master Lock gate and ball valve lockout devices work in difficult applications like tight spaces and insulated pipes.

Rotating Gate Valve Lockouts

Outward/Inward Rotation Allows for Easier Installation & Storage

- ▶ Surrounds the valve operating handle to protect against accidental valve opening
- ▶ Multiple workers can apply their lockout hasps or personal safety locks
- ▶ Tough, lightweight, dielectric Zenex™ Thermoplastic bodies withstand chemicals; perform effectively in extreme conditions
- ▶ Unique, patented rotating design allows for easier installation in confined space applications
- ▶ Complete with high-visibility permanent safety labels (English, French & Spanish) that can be written-on to identify the responsible person, then erased for the next job
- ▶ Center knockout can be removed for rising stem gate valves
- ▶ Each size rotates into itself and nests within the next larger size to save space in storage

Master Lock Model #	Description	Depth	Stem Opening
480	1 in to 3 in dia. valve handles	1-1/16 in	3/4 in
481	2 in to 5 in dia. valve handles	1-1/2 in	1-1/2 in
482	4 in to 6.5 in dia. valve handles	1-7/8 in	2-1/2 in
483	6 in to 10 in dia. valve handles	2-3/4 in	3-1/2 in
484	8 in to 13 in dia. valve handles	3-3/8 in	4 in
485	1 set of 480-484		

Easy to Store Fits in Kits



Pressurized Gas Valve Lockout

Fits Pressurized Gas Valves

- ▶ Patented design works with valve guard in place
- ▶ Fits virtually all pressurized gas valve handles up to 3in diameter
- ▶ Compact size easily stored when not being used
- ▶ Accepts any Master Lock® or American Lock® Safety Padlock
- ▶ Works with lockout hasps for multiple worker lockout

Master Lock Model #	Description	Depth	Stem Opening
S3910	Pressurized Gas Valve Lockout	1in	1-5/8in



Ball Valve Lockout Devices

Effective Lockout for Virtually Any Ball Valve

- ▶ Easy to use – simple, intuitive designs
- ▶ Broad application
 - Devices could lock up ball valves up to 4in
 - Fit virtually all types of pipe including insulated, PVC and metal
- ▶ Lightweight and compact – devices are easy to carry, store and apply even in tight, awkward spaces



S3068 Seal Tight™ Handle-On Lockout

Metal device clamps tight on handle stop. Defies corrosive environments and extreme temperatures.



468L Seal Tight™ Handle-Off Lockout

Device encloses the valve stem, with the handle removed, to make accidental reactivation virtually impossible. Operates in extreme temperatures.




S3081 Adjustable Lockout

Works with S806 cable lockout device for the most secure fit.



S3476/S3477 1/4 Turn Ball Valve Lockout

Fits manual, quarter turn ball valve handles to protect against accidental opening. Easy to use one piece design locks valve in OFF position. Two rows of lock out points allow for a secure fit.



Master Lock Model #	Description	For Valve Diameters of:
S3068	Seal Tight™ Handle-On Ball Valve Lockout 5-3/4in L x 2-1/8in W x 2-1/2in H	1/4in to 4in
468L	Seal Tight™ Handle-Off Lockout, 11-1/2in H x 12-3/4in W x 2-1/2in D	3/8in to 4in
S1000	Seal Tight™ Ball Valve Lockout Kit (Set of 1 Each S3068 & 468L)	1/4in to 4in
S3081	Adjustable Ball Valve Lockout	1/2in to 2in

Master Lock Model #	Description
S3476	Fits valves between 1/4in (6.35mm) to 1in (25mm) diameter
S3477	Fits valves between 1-1/4in (31mm) to 3in (76mm)

Custom Lockout Kits & Stations

Tailor the Mix of Master Lock Lockout Products for Your Safety Requirements

You can determine the mix of Master Lock lockout products for your unique safety requirements in **2 Easy Steps!** Master Lock then packs each kit or station.

- ▶ **1. Choose an assortment of Master Lock padlocks, lockout devices, and tags to satisfy specific employee needs**



ALL padlock models and lockout devices are available!

- ▶ **2. Choose any portable lockout kit or wall-mount station to store your newly selected assortment**



- ▶ Custom kits and stations are priced at the total of all components - padlocks, devices, tags, and the kit
- ▶ Customers, please contact your preferred Master Lock Distributor to specify the contents of your kits. Distributors, contact Master Lock Safety Specialists at 800-944-1380 to process the order
- ▶ Minimums apply. Laser Engraving and Guardian Extreme™ products excluded

Custom Lockout Kits & Stations

Select your own unique assortment of safety padlocks, lockout devices, tags, and the kit or station that meets your needs.