

Padlocks

Medeco M³ & X4 CLIQ padlocks are available to provide accountability in a weather resistant padlock that can be used in indoor or outdoor applications. Padlocks have robust reprogramming abilities, as well as audit and scheduling capabilities. Outstanding performance for your perimeter fences and gates, or access to equipment storage areas where traditional EAC is practically impossible to install.



Medeco M³ & X4 CLIQ Padlock Cylinders

Description	Part Number	Price	M ³	X4
Cylinder for Medeco Protector II (50) Series Padlock	500020		•	
Cylinder for Medeco System (54) Series Padlock	510600		•	•
Cylinder for Abus Padlock Series 83KNK/45, 83KNK/50 & 83KNK/55. (Use Abus driver M)	2020000		•	•
Cylinder for American 3600/3700 Padlock (Use American driver DR-MED6)	2020000		•	•
Cylinder for New Standard Padlock	2020052		•	
Cylinder for Master 20 and 6600, 6700 Pro Series (Use Master driver 0298-627)	2020000		•	•
Cylinder for Schlage 45-101 padlock	2020074		•	•

Medeco M³ & X4 CLIQ Protector II Padlocks (Includes Cylinder)

Description	Part Number	Price	M ³	X4
Large Body - 7/16" dia shackle, 1 3/8" clearance	5004732		•	
Large Body - 7/16" dia shackle, 1 3/8" clearance, Dust cover	50047321		•	
Large Body - 7/16" dia shackle, 1 7/8" clearance	5004832		•	
Large Body - 7/16" dia shackle, 1 7/8" clearance, Dust cover	50048321		•	
Med Body - 5/16" dia shackle, 1 3/8" clearance	5004734		•	
Med Body - 5/16" dia shackle, 1 3/8" clearance, Dust cover	50047341		•	
Med Body - 5/16" dia shackle, 1 7/8" clearance	5004834		•	
Med Body - 5/16" dia shackle, 1 7/8" clearance, Dust cover	50048341		•	

Medeco M³ & X4 CLIQ System Series Padlocks (Includes Cylinder)

Description	Part Number	Price	M ³	X4
Padlock 5/16" Shackle - KIK				
Indoor/Outdoor Padlock, 1 1/8" Shackle Clearance	54515X0		•	•
Indoor/Outdoor Padlock, 2 3/8" Shackle Clearance	5451FX0		•	•
Shrouded Padlock, 3/4" Shackle Clearance	54525X0		•	•
Padlock 5/16" Shackle - 6 Pin LFIC				
Indoor/Outdoor Padlock, 1 1/8" Shackle Clearance	54615X0		•	
Indoor/Outdoor Padlock, 2 3/8" Shackle Clearance	5461FX0		•	
Shrouded Padlock, 3/4" Shackle Clearance	54625X0		•	
Padlock 7/16" Shackle - KIK				
Indoor/Outdoor Padlock, 1 3/8" Shackle Clearance	54715X0		•	•
Indoor/Outdoor Padlock, 1 7/8" Shackle Clearance	5471FX0		•	•
Shrouded Padlock, 3/4" Shackle Clearance	54725X0		•	•
Padlock 7/16" Shackle - 6 Pin LFIC				
Indoor/Outdoor Padlock, 1 3/8" Shackle Clearance	54815X0		•	
Indoor/Outdoor Padlock, 1 7/8" Shackle Clearance	5481FX0		•	
Shrouded Padlock, 3/4" Shackle Clearance	54825X0		•	

* 0 = Non-key retaining and R = key retaining

Medeco³

High Security Cylinders & Locking Systems

Medeco³ High Security Cylinders feature UL437 Listed physical strength components like the triple locking technology for ultimate pick resistance and solid brass construction with strategically placed hardened inserts to thwart drilling attacks.

Passing UL437 and BHMA's rigid testing procedures reaffirms Medeco³'s ability to protect people and property. Medeco³ builds on Medeco's over 40 years of lock engineering innovation and takes security to the next level while still offering the highest level of protection against unauthorized key duplication.



Patented Key Control

Protects against unauthorized duplication of your keys.



Uses Existing Hardware

Can be master keyed into a system containing Medeco BiLevel and Medeco³ mechanical as well as M³ CLIQ eCylinders. Medeco³ cylinders are available in a wide variety of formats, retrofitting most hardware on the market today.



Can Be Master Keyed

Can be master keyed into a system containing Medeco BiLevel and Medeco³ mechanical as well as M³ CLIQ eCylinders.



Protection From Physical Attack

Medeco³ cylinders are UL 437 Listed and stand up to drilling, picking and other forms of physical attack.



Special Angle Cut Keys

Requires a special key cutting machine and access to Medeco specific blanks, available in a variety of restrictions to support every need.



Picking and Bumping Protection

Medeco³ cylinders use a sidebar that prevent the key from rotating until it is elevated, rotated and aligned in the correct position. This feature protects against bumping and picking attacks.

Technical Information:

- 40,000 cycle endurance test
- Resistance to picking or key fitting tests
- **UL437:**
 - Tests prescribed in Underwriters Laboratory Standard for Safety for Key Locks are primarily designed to measure a locking cylinder's ability to resist physical attack.
- **ANSI/BHMA A156.30:**
 - Builders Hardware Manufacturing Association (BHMA) standards are certified by the American National Standards Institute (ANSI) which works with industry leaders to provide manufacturers and consumers with product quality and performance ratings based on preset criteria and standardized testing.
 - BHMA standard A156.30-2003, approved and adopted by ANSI, covers high security cylinders and was developed by BHMA to provide specific guidance as to which products can be considered as high security cylinders.
 - Medeco³ cylinders have been tested to BHMA's highest certification level by an independent laboratory and achieved certification in the high security cylinders category.
 - The cylinders meet or exceed BHMA A156.30 criteria for strength and durability, key control, and surreptitious entry resistance.

Applications:

- Medeco³ retrofit cylinders are ideal for any application requiring key control and physical security of your cylinders

Warranty:


Medeco³ cylinders are warranted for two years against manufacturer's defects. See the Medeco[®] limited warranty for full details

How To Order Key-in-Knob/Lever Cylinders

Complete part numbers are required for all orders. To determine the correct part number, fill in the "X's" in sequential order.

1	2	3	4	5			
200200S1 base part #	T cylinder	05 finish	LT keyway	S pinning			
Refer to pages 71-89 for descriptions and technical specifications to find the corresponding base part number.	<ul style="list-style-type: none">– = OriginalK = Medeco KMT = Medeco³W = BiaxialJ = Medeco³ BiLevelC = Classic CLIQN = Medeco X4S = M³ CLIQM = Medeco X4 CLIQ	<p>Refer to the inside back cover of this catalog for finish options. Include the corresponding two digit finish number.</p> <p>Upcharge for split finish.</p>	<p>Insert keyway if known or contact Customer Service for help.</p>	<table><tr><td>S = Sub-Assembled (Uncombined) No additional information needed</td><td>P = Pinned (Combined) Keyed alike (KA) Keyed different (KD) 2 keys per cylinder</td><td>M = Master Keyed Provide specific pinning or contact Customer Service for support Must specify quantity for keys.</td></tr></table>	S = Sub-Assembled (Uncombined) No additional information needed	P = Pinned (Combined) Keyed alike (KA) Keyed different (KD) 2 keys per cylinder	M = Master Keyed Provide specific pinning or contact Customer Service for support Must specify quantity for keys.
S = Sub-Assembled (Uncombined) No additional information needed	P = Pinned (Combined) Keyed alike (KA) Keyed different (KD) 2 keys per cylinder	M = Master Keyed Provide specific pinning or contact Customer Service for support Must specify quantity for keys.					


BUILD A KEY-IN-KNOB/LEVER PART #:




**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:
 T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ,
 “-” = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.

Note: (P) refers to **Pinned** and (S) to **Sub-Assembled** at the end of each part string in the price book.


Medeco System Series Padlock Cylinders

Description	Part Number	M ³	BiLevel	X4	Biax/Orig	KeyMark
 6 Pin cylinder for System Series KIK style padlocks	510600 (P)					
	510600 (S)					

New Standard Mfg. Co.® Padlock Cylinders

Description	Part Number	M ³	BiLevel	X4	Biax/Orig	KeyMark
 6 Pin Cylinder for New Standard® Padlocks	2020052 (P)					
	2020052 (S)					

Schlage® Padlock Cylinders

Description	Part Number	M ³	BiLevel	X4	Biax/Orig	KeyMark
 6 Pin Cylinder for Schlage® 45-101 Padlock	2020074 (P)					
	2020074 (S)					

KIK/KIL Cylinder Components

Description	Part Number	Price
Medeco ³ slider package. (Includes slider & spring)	940174	
Medeco BiLevel slider package	940227	
Flat Head Machine Screw, 5/16" -#2-56 UNC, Phillips with Nylok Patch for 20-200XX Cylinders. Sold in Bags of 100	CP-010203-050	
Pan Head Machine Screw, 1/4" - #2-56 UNC, Phillips with Nylok Patch for most Lazy Motion Cylinders. Sold in Bags of 100	CP-010503-040	
Retaining Ring, Knob Cylinder "E" Clip	CP-020020	
Retaining Ring, Knob Cylinder, Full Clip	CP-020040	
Retaining Ring, Knob Cylinder Plug Retainer, "C" Clip	CP-020100	
Lazy Motion Tailpiece Retainer for 20*090X cylinders	CP-021031	
Tailpiece Retainer ring for Arrow and Sargent clip on tailpieces	CP-021130	
Plug Retainer, Standard Knob	CP-021370	
Castle Nut Retainer for Schlage type lazy motion cylinders	CP-021651	
Compression Spring for Schlage type lazy motion cylinders	CP-030670	
Drive Disk for Schlage -type Lazy Motion Cylinders	CP-041200	
Detent Pin for Schlage type lazy motion cylinders	CP-064490	

KIK/KIL Cylinder Plugs

Description	Part Number	Price
Plug for 20-200XX- (Medeco Original)	12126002 -	
Plug for 20W200XX (Medeco Biaxial)	12126156 W	
Plug for 20T200XX (Medeco ³)	1212633 T	

Mailbox Lock Cylinders

Description	Part Number	(S) Pricing	(P) Pricing
6 Pin Medeco ³ Rim Style Mailbox cylinder, less slider	490357 T		
6 Pin Medeco ³ Key in Knob Style Mailbox cylinder, less slider	490375 T		
6 Pin Medeco ³ BiLevel Mailbox cylinder	200104 J		
6 Pin Mailbox cylinder. Medeco KM only	200155 K		
6 Pin Mailbox cylinder	200156 N		

**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:
 T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ,
 "-" = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.

Note: (P) refers to **Pinned** and (S) to **Sub-Assembled** at the end of each part string in the price book.