

Mortise Components

Description	Part Number	Price
1-1/2" Dia. Threaded Adapter Ring for Corbin® Jumbo Mortise Cylinder (converts conventional size Mortise Cylinder to Jumbo thread size) Contains: CP-050131 Adapter Ring and CP-011013-030		
# 8-32 x 3/16" Set Screws	940010	
Medeco ³ Slider Package, Includes Slider & Spring	94-0174-XX	
Medeco ³ BiLevel slider package	94-0227-XX	
# 2-56 UNC x 5/16" Length Phillips® Head Screws- Stainless Steel (used to attach cams to Mortise Cylinders)	CP-010203-050	
Set Screws (for Medeco X4 pin chamber) # 6-32 x 1/8"	CP-011011-020	
Set Screws (for High Security pin chambers) #8-32 x 1/8"	CP-011013-020	
Cam Washer for Mortise Cylinders	CP-021011	
Sidebar Spring-Stainless Steel	CP-030018	
Mounting Nut for Mortise Cylinder 1.150"-32 UNS Inside Dia.	CP-050120	
5 Pin Sidebar Assembly, .123" high for Door Hardware Cylinders	CP-084571	
6 Pin Sidebar Assembly, .123" high for Door Hardware Cylinders	CP-084671	

Rim Cylinders

Description	Part Number	M ³	BiLevel	X4	Biax/Orig	KeyMark
5 Pin 1-1/16" Rim Cylinder - Horizontal Tailpiece	100300H (P) 100300H (S)					
5 Pin 1-1/16" Rim Cylinder - Vertical Tailpiece	100300V (P) 100300V (S)					
5 Pin 1-1/16" Rim Cylinder, Sargent® Mounting Style, Horizontal Tailpiece	100305H (P) 100305H (S)					
5 Pin 1-1/16" Rim Cylinder, Sargent® Mounting Style, Vertical Tailpiece	100305V (P) 100305V (S)					
5 Pin 1-1/16" Rim Cylinder, 180 Degree Lazy Motion	100600 (P) 100600 (S)					
6 Pin, 1-1/8" Rim Cylinder Horizontal Tailpiece	100400H (P) 100400H (S)					
6 Pin, 1-1/8" Rim Cylinder Vertical Tailpiece	100400V (P) 100400V (S)					
6 Pin 1-1/8" Rim Cylinder- Sargent® Mounting Style, Horizontal Tailpiece	100403H (P) 100403H (S)					
6 Pin 1-1/8" Rim Cylinder- Sargent® Mounting Style, Vertical Tailpiece	100403V (P) 100403V (S)					
6 Pin 1-1/8" Rim Cylinder, 180 Degree Lazy Motion	100700 (P) 100700 (S)					
6 Pin Jumbo Rim Cylinder Corbin Russwin® Master Ring Cylinder Replacement	101355 (P) 101355 (S)					
6 Pin 1-15/32" Rim Cylinder with Extended Plug and Horizontal Tailpiece	104407HA (P) 104407HA (S)					

6 Pin high security cylinders are available in 7 Pin in Medeco X4.
Check the eCylinder section for pricing and technology available.

**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:
T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ,
"-" = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.
Note: (P) refers to **Pinned** and **(S)** to **Sub-Assembled** at the end of each part string in the price book.

Rim Cylinder Plugs

Description	Part Number	Price
Plug for 10-0300H or 10-0300V (Medeco Original®)	12001002 -	
Plug for 10W0300H & 10W0300V (Medeco Biaxial®)	12001006 W	
Plug for 10T0300 (Medeco ³ ®)	1200100 T	
Plug for 10-0400H or 10-0400V (Medeco Original®)	12030002 -	
Plug for 10W0400H & 10W0400V (Medeco Biaxial®)	12030006 W	
Plug for 10T0400 (Medeco ³ ®)	1203000 T	
Plug for 10J0300 (Medeco BiLevel®)	1238900 J	
Plug for 10J0400 (Medeco BiLevel®)	1251200 J	

Add finish and keyway to all part #'s .

Medeco³ or Medeco BiLevel Slider package sold separately .

Rim Components

Description	Part Number	Price
Medeco ³ Slider Package, Includes Slider & Spring	94-0174-XX	
Medeco BiLevel slider package	94-0227-XX	
Set Screws (for Medeco X4 pin chamber) #6-32 x1/8"	CP-011011-020	
Set Screws (for HS pin chambers) #8-32 x1/8"	CP-011013-020	
Rim Cylinder Mounting Screws (#12-24 UNF x 1 57/64" Length)	CP-012917-000	
Rim Cylinder Plug Retainer	CP-020010	
Screw-on Cap Rim Tailpiece Retainer	CP-021121	
Sidebar Spring-Stainless Steel	CP-030018	
Back of Plug Roll Pin 3/32" Dia. x .437" Length	CP-060203	
5 Pin Sidebar Assembly, .123" high for Door Hardware Cylinders	CP-084571	
6 Pin Sidebar Assembly, .123" high for Door Hardware Cylinders	CP-084671	
Rim Cylinder Mounting Plate	CP-180031	

**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:

T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ, "-" = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.

Note: (P) refers to **Pinned** and **(S)** to **Sub-Assembled** at the end of each part string in the price book.

Caps (Sold in bags of 100)

Description	Part Number	Price
Medeco X4 I/C Pin Spring Caps (Stamped) (for rekeying)	CP-170430	
Medeco X4 I/C Pin Spring Caps (Machined) (for new cylinder)	CP-170440	
6 Pin Spring Covers for Medeco 32 & 31 Series I/C, Sargent, KeyMark Corbin (7Pin) Medeco X4 Yale (6&7 Pin), Brass, 1.010" Length	CP-170011	
5 Pin Spring Covers for Medeco 32 Series I/C, Cams and Switch Lock Plugs, Brass, .840" Length	CP-170021	
3 Pin Spring Covers for Cam and Switch Lock Plugs, Brass, .500" Length	CP-170031	
4 Pin Spring Covers for Cam and Switch Lock Plugs, Brass, .670"	CP-170041	
6 Pin Spring Covers for Medeco and Medeco X4 20 Series Key-in-Knob Cyls, Medeco X4 Schlage LFIC, Stainless Steel, .980" - Old Style	CP-170051	
5 Pin Spring Covers for Medeco 20 Series Key-in-Knob Cyls, Stainless Steel, .810" - Old Style	CP-170061	
6 Pin Spring Covers for Medeco ³ 32*0202 Removable Cylinder for 50 Series Brass Body Padlocks, Brass, 1.010" (Notch in cover for steel ball bearing retainer)	CP-170271	
6 Pin Spring Covers for Medeco & Medeco X4 20 Series Key-in-Knob Cylinders & Medeco X4 Schlage Style LFIC	CP-170730-6	
5 Pin Spring Covers for Medeco 20 Series Key-in-Knob Cylinders	CP-170730-5	

Springs (Sold in bags of 100)

Description	Part Number	Price
Tumbler Springs, 10 Series Door Hardware	CP-030001	
Tumbler Springs, 60 Series Cam & Switch Locks	CP-030017	
Sidebar Springs	CP-030018	
Tumbler Springs, 32 Series (stainless steel)	CP-030042	
Medeco ³ Slider Springs	CP-030910	
Medeco X4 Springs (Bag of 300)	CP-030590	

**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:
T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ,
"." = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.

Note: (P) refers to **Pinned** and (S) to **Sub-Assembled** at the end of each part string in the price book.