










Collars & Cylinder Rings
















	Description	Part Number	Price
	Tapered Cylinder Collar	94-0188-XX	
	1/4" Thick Spacer Ring 1.165" Inside Diameter x 1.375 Outside Diameter	CP-070011	
	1/8" Thick Spacer Ring 1.165" Inside Diameter x 1.375 Outside Diameter	CP-070451	
	Raised Cylinder Ring	CP-180021	
	Flush Cylinder Ring	CP-180041	
	Adjustable Cylinder Collar	CP-160180	

Rim Tailpieces

	Description	Part Number	Price
	Tailpiece for Rim Cylinder (155/64") Before 1980, After 1983	CT-Y02	
	Lazy Motion Tailpiece (2 29/64")	CT-Y08	
	Tailpiece for Rim Cylinder (2 9/16")	CT-Y32	

**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:
T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ,
“-” = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.
Note: (P) refers to **Pinned** and **(S)** to **Sub-Assembled** at the end of each part string in the price book.

KIK/KIL Cylinder Tailpieces

Description	Part Number	Price
 Tailpiece for Schlage® B200, B400, B500, Series (Double Cylinder)	CT-F34	
 Tailpiece for Schlage® F160, B100, B200, B400, B500 Series (Double Cylinder)	CT-F35	
 Tailpiece for Schlage® B200, B400 Series (Double Cylinder)	CT-F36	
 Tailpiece for Schlage® F160, B100, B200, B400, B500 Series (Double Cylinder)	CT-F37	
 Tailpiece for Schlage® "E", F160, "H", B100, B200, B400, B500 Series (Single Cylinder)	CT-F38	
 Tailpiece for Baldwin® Images Series	CT-F40	
 Tailpiece for Marks® 190S Lever Lockset	CT-V00	
 Tailpiece for Marks® 190AB Lever Lockset	CT-V01	
 Tailpiece for PDQ® SP	CT-V02	
 Tailpiece for Falcon® "T" Series	CT-V03	
 Tailpiece for Corbin® Russwin® 3900 Series Lever Lock	CT-V19	
 Tailpiece for Sargent® 11 Line TZone	CT-V35	
 Tailpiece for Anderson® Door Locks	CT-V39	
 Tailpiece for Kwikset®	CT-V40	
 Tailpiece for Schlage® Lazy Motion	CT-Y08	

**Refer to the eCylinder section for more detail on specific technologies available and pricing. Technologies are represented by the following letters:
T = Medeco³, S = M³ CLIQ, J = Medeco³ BiLevel, W = Biaxial, V = Medeco Biaxial CLIQ, K = Medeco KM, N = Medeco X4, C = Classic CLIQ, M = Medeco X4 CLIQ,
"-" = Original, Z = Medeco Original KW CLIQ, G = Medeco XT ***See key section for surcharges for custom coined cut keys or special stamping requirements.
Note: (P) refers to **Pinned** and (S) to **Sub-Assembled** at the end of each part string in the price book.