

High Quality Varifocal Auto-Iris Megapixel IR Lenses



1/2.7" - 3 Megapixel

VF2812IRMP3 – 2.8~12mm Varifocal IR Lens

FEATURES:

- ◆ 3MP Resolution
- ◆ 2.8 ~ 12mm Varifocal
- ◆ IR Corrective
- ◆ CS Mounting
- ◆ DC Driven Auto Iris
- ◆ Composite Body
- ◆ Full Glass Elements



1/3" - 2 Megapixel

VF550IRMP2 – 5~50mm Varifocal IR Lens

FEATURES:

- ◆ 2MP Resolution
- ◆ 5 ~ 50mm Varifocal
- ◆ IR Corrective
- ◆ CS Mounting
- ◆ DC Driven Auto Iris
- ◆ All Metal Body
- ◆ Full Glass Elements



SPECIFICATION		VF2812IRMP3		
Megapixel Resolution	3MP			
Focal Length	2.8 ~ 12mm			
Aperture	F1.4			
Auto Iris	Yes - DC Driven			
IR Corrective	Yes			
Mounting	CS			
Format	1/2.7"			
Lens Body	Composite			
Lense Structure	8 Groups/8 Elements			
Field of View	Diagonal	Horizontal	Vertical	
	127° ~ 40°	112° ~ 35°	59° ~ 19°	
Dimensions (w/Auto Iris)	43mm (H) x 40mm (W)			
Barrel Diamter	28mm			
Weight	0.1lb			

Note: Specification subject to change without notice

Notes: specification subject to change without notice

SPECIFICATION		VF550IRMP2		
Megapixel Resolution	2MP			
Focal Length	5 ~ 50mm			
Aperture	F1.6			
Auto Iris	Yes - DC Driven			
IR Corrective	Yes			
Mounting	CS			
Format	1/3"			
Lens Body	Metal			
Lense Structure	8 Groups/12 Elements			
Field of View	Diagonal	Horizontal	Vertical	
	63° ~ 6°	55° ~ 5°	31° ~ 3°	
Dimensions (w/Auto Iris)	70mm (H) x 50mm (W)			
Barrel Diamter	39mm			
Weight	0.25lb			