# Northern \*


## HDDWIDE

### 4-in-1, Full HD 1080p Outdoor Eyeball Camera 60' IR Range, 2.5mm - 150° FOV


#### FEATURES:

- 1/2.9" Sony CMOS Sensor
- Multi Format (TVI, CVI, AHD, 960H) ٠
- Full HD 1080p Resolution ٠
- 2.5mm/150° FOV Ultra Wide Angle Lens
- 24 IR LED's / 60' IR Range ٠
- True Day/Night Mechanical IR Cut Filter ٠
- **Digital Wide Dynamic Range** ٠
- Cable & UTC OSD Control ٠
- **3-Axis Wall or Ceiling Mountable** ٠
- Sense-up / Slow Shutter Speed ٠
- **3D Digital Noise Reduction** ٠
- 12 Volt DC power / IP66 Weatherproof ٠

#### **CAMERA OVERVIEW:**



Side View / Bottom View & Mounting Configuration



#### INCLUDED ACCESSORIES:

- 1. Camera
- 1. User Manual
- 1. Mounting Screws



In-Line **Cable Mounted** OSD Control

Note: Specification subject to change without notice



	TVI
(	CVI
	AHD
(	960H

SPECIFICATION	HDDWIDE
Image Sensor	1/2.9" Sony CMOS Sensor
Total Pixels	1984 x 1225
Active Pixels	1920 x 1080
Resolution	1920 x 1080 (1080p)
Scanning System	Progressive Scan
Dual OSD Control Access (On Screen Display)	Cable Mounted Joystick Controlled / UTC (coaxial) Controlled
Digital WDR (Wide Dynamic Range)	Auto / Off / On - 0 ~ 8 Adjustable
DNR (Digital Noise Reduction)	2D & 3D, Low, Middle, High, Of
Video Output	TVI, CVI, AHD & 960H Selectable via OSD Joystick
Lens Type - True Day Night	2.5mm Ultra-Wide Angle Fixed Lens (150° FOV)
Sense-up	Off / Auto (x2 ~ x30 Selectable)
Shutter Speed	Auto, FLK, 1/30 ~ 1/50,000, x2 ~ x30
IR Cut Filter	Built in Mechanical
Minimum Illumination	Color 1.0 Lux, B/W 0.5 Lux, IR LED ON 0.0 Lux
IR LED Count / Range	24 IR LED's / 60' Range / 850nM
S/N Ratio	More than 50dB
Automatic Gain Control	0 ~15 Adjustable
Sync System	Internal
Gamma Characteristics	y = 0.45 typ
White Balance	AWB / ATW / AWC->Set / Indoor / Outdoor / Manual
Back Light Compensation	Off / BLC / HSBLC
HBLC (High Back Light Compensation)	On / Of
Day/Night	EXT / Auto / Color / B/W
Mirror	Mirror / V-Flip / Rotate / Of
Languages	English, French, Spanish, German, Italian (see OSD Menu for more)
Brightness	0 ~100 Adjustable
Motion Detection	On/Off (4 Zone Selectable)
Privacy Mask	On/Off (4 Zone Selectable)
Power Input	12VDC Only
Power Requirement	130mA / 350mA IR LED ON
Overall Camera Dimensions	3.76"(W) x 3.15"(H) (70mm x 80mm)
Housing / Color	Aluminum / White
Weight	.89 Lb.
Operating Temperature	-14°F ~ 122°F
Weatherproof Rating	IP66

Northern<sup>2</sup>