

## AC2450VA 24 Volt AC 50VA Plug-in Transformer



AC2450VA

### FEATURES

- ◆ Class II, UL Listed
- ◆ 120 Volt AC Input
- ◆ Screw Terminal Connection
- ◆ 50VA (2 Amp) Output
- ◆ Safety Screw Wall Outlet

### SPECIFICATION

### AC2450VA

Type	Class II UL Listed
Input	AC 120V
Output	24 Volt AC 2 Amp
Connection	Screw Terminal

## 24VACTO12VDC8 24 Volt AC to 12 Volt DC Power Converter



24VACTO12VDC8

### FEATURES

- ◆ 24VAC Input Power
- ◆ 800mA Regulated 12VDC Output
- ◆ Dimensions 2.4" x 1.9" x 1.0" w/o cable & connection

### SPECIFICATION

### 24VACTO12VDC8

Application	Power Converter
Input	24VAC
Output	12 Volt DC (Regulated)
Dimensions W x H x D	2.4" x 1.9" x 1.0" (with 18" Lead-in / 18" Lead-out)

Note: Specification subject to change without notice