



4.0 Megapixel IP, True WDR, Motorized Outdoor IR Bullet Camera

POE, Full HD 1080P, 2.8-12mm IR Lens, 100' IR, IP66



Side



Front

Base

	SPECIFICATION	IP4MVFB
CAMERA	Image Sensor	1/3" Progressive Scan CMOS
	Minimum Illumination	0.014 lux@ F1.2, AGC on / 0 lux with IR
	IRLED Count / Range / Nanometer	42 IR LED's / 100' Range / 850nm
	Shutter Time	1/3 s to 1/10,000 s
	Lens (IR Corrective)	Motorized 2.8-12mm @ F1.4, angle of view: 112° ~ 33.8°
	Lens Mount	Ø14
	Camera Bracket Adjustment	3-Axis Design
	Day & Night	Yes - IR Filter with Auto Switch
	DNR (Digital Noise Reduction)	3D DNR
	True Wide Dynamic Range	120dB WDR
BLC (Backlight Compensation)	Yes, Zone Configurable	
On-board storage	Built-in Micro SD/SDHC/SDXC card slot, up to 128GB	
Smart Analytic Features	Line crossing detection, intrusion detection	
Region of Interest	Yes	
COMPRESSION	Video Compression	H.264 / MJPEG / H.264+
	H.264 Codec Profile / Bit Rate	Main Profile / 32 Kbps ~ 16 Mbps
	Dual Streaming	Yes
	Audio Compression	G.711/G.722.1/G.726/MP2L2
Audio Bit Rate	64 Kbps (G.711)/16 Kbps (G.722.1)/16 Kbps (G.726)/32 to 128 Kbps (MP2L2)	
IMAGE	Maximum Image Resolution	2688 x 1520
	Frame Rate	20fps (2688 x 1520), 30fps (1920 x 1080, 1280 x 720)
	Image settings	Compression, Color, Saturation, Brightness, Contrast, Sharpness, Rotate Mode, Privacy Mask
NETWORK	Network Storage	NAS (supports NFS, SMB/CIFS), ANR
	Alarm Trigger	Motion Detection, Line Crossing Detection, Intrusion Detection, Tamper Alarm, Network Disconnect, IP Address Conflict, Storage Exception
	Protocols	TCP/IP, UDP, ICMP, HTTP, HTTPS, FTP, DHCP, DNS, DDNS, RTP, RTSP, RTCP, PPPoE, NTP, UPnP, SMTP, SNMP, IGMP, 802.1X, QoS, IPv6, Bonjour
	System Compatibility	ONVIF (PROFILE S, PROFILE G), PSIA, CGI, ISAPI
	Security Functions	Three level user authentication, password authorization, HTTPS and SSH certificate, IEEE802.1X, basic and digest authentication, watermark, IP address filtering, log-in lockout
INTERFACE	Communication Interface	1 RJ45 10M / 100M Ethernet port
	Alarm Interface	1x Alarm I/O - Bare Lead
	Audio Interface	1x Audio Line In/Out - Bare Lead
GENERAL	Operating Conditions	-30°C ~ 60°C (-22°F ~ 140°F) humidity 95% or less (non-condensing)
	Housing Color	White
	Housing Material	Heavy Duty Aluminum
	Power Supply	12 VDC ± 10%, PoE (802.3af)
	Power Consumption	Max. 7.5 W with IR on
	Weatherproof Rating	IP66
	Dimensions	95 mm x 105 mm x 259 mm (3.74" x 4.13" x 10.8")
	Weight	1200 g (2.65 lbs)
Certifications	UL / CUL	

FEATURES

- ◆ Full HD 1080p Real Time Video
- ◆ True Wide Dynamic Range - 120dB
- ◆ Up to 2688 x 1520 Resolution (20FPS)
- ◆ Motorized 2.8-12mm Varifocal IR Lens
- ◆ POE - Power over Ethernet
- ◆ Free CMS & IP Server Software
- ◆ SD Card Slot (Card Sold Separately)
- ◆ 3D Digital Noise Reduction
- ◆ Mechanical IR Cut Filter
- ◆ 42 IR LED's - 100' IR Range
- ◆ ONVIF / PSIA / CGI Compliant
- ◆ Audio Line In/Out & Alarm
- ◆ IP66 Weatherproof
- ◆ UL/CUL Certified

INCLUDED ACCESSORIES

1. Quick Guide
1. Software Disc
1. Mounting Template & Hardware Packet
1. Junction Box
1. L-Style Wrench
1. Video Test Connector

Note: Specification subject to change without notice