



# M490DE

Delayed egress  
electromagnetic lock



## Overview

The Schlage M490DE delayed egress electromagnetic lock is designed to meet NFPA 101 Life Safety Code while providing the same robust, easy-to-install, security of our M400 Series magnetic locks. The M490DE has a 15-second delayed egress timer with audible alarm which can be configured to trigger by an internal “plunger switch,” or by external contacts, such as a request-to-exit push bar.

All M400 Series electromagnetic locks are symmetrical with field-selectable handing, allowing optimum placement of the magnet no matter the application. They are designed to provide automatic voltage sensing for 12 and 24 volts along with polarity protection to make wiring less complex. M490DE models are tested and certified to meet or exceed UL special locking arrangements and BHMA 1500 lb hold force requirements.

M490DE electromagnetic locks come in four configurations to meet your specific security needs. Single and double door models are offered in standard configurations. Plus versions of these models with “P” designations add intelligent sensing and reporting features needed to integrate with access control systems.

This easy-to-install, cost effective solution provides maximum access security and safety.

## Features and benefits

- 1500 lb. hold force rating for maximum security applications
- 15 second delay - activated by internal plunger switch or auxiliary input
- LED Indication with audible alerts
- Release input, reset input, fire alarm input
- Plus models offer magnetic bond sensor (MBS), adjustable relock time delay (RTD) and door position switch (DPS)
- Automatic voltage selection (AVS)
- Bayonet mount simplifies installation by eliminating the need to hold lock overhead while securing
- Armature pivot feature compensates for slight opening imperfections
- Aluminum housing in 628 satin finish
- UL special locking arrangements, UL 10C, cUL, CSFM certifications
- Meets NFPA 101 life safety code
- BOCA compliant option available
- Limited lifetime warranty on magnetic coil assembly

## Standard features

### ALL MODELS

- Auto Voltage Selection (AVS) senses the voltage applied to lock and responds accordingly
- Internal plunger switch activates delayed egress timer

### Optional accessories

- Herculite door bracket kit (HDB)

### M490DEP/M490DEP-2

- Magnetic Bond Sensor (MBS) monitors the strength of the bond between the lock and armature so you know the door is secure
- Door Position Switch (DPS) monitors whether the door is open or closed
- BOCA compliant (upon request) with options for 15- or 30-second time delay

## Ordering information

### STANDARD MODELS

- M490DE** - Single lock, 15-second delay
- M490DE-2** - Double lock, separate housing, 15-second delay

### Optional preset

- M490DE-30S** - Single lock, factory set 30-second delay (requires fire marshal letter of approval)

### PLUS MODELS

- M490DEP** - Single lock, 15-second delay
- M490DEP-2** - Double lock, 15-second delay
- M490DEP-BC** - BOCA compliant single lock, factory set 15-second delay with auto re-armed and locked state after door is opened and re-closes
- M490DEP-BC30S** - BOCA compliant single lock, factory set 30-second delay with auto re-armed and locked state after door is opened and re-closes (requires fire marshal letter of approval)

## M490DE electromagnetic delayed egress lock specifications

| Specification                 | M490DE/M490DEP                                   | M490DE-2/M490DEP-2                                       |
|-------------------------------|--------------------------------------------------|----------------------------------------------------------|
| Holding force                 | Meets or exceeds BHMA standard of 1500 lbs       | Meets or exceeds BHMA standard of 1500 lbs per door leaf |
| Input voltage (auto selected) | 12/24 VDC                                        | 12/24 VDC                                                |
| Current draw                  | .75A @ 12 VDC<br>.45A @ 24 VDC                   | 1.25A @ 12 VDC<br>.76A @ 24 VDC                          |
| Height                        | 3"                                               | 3"                                                       |
| Length                        | 12 1/2"                                          | 25 1/16"                                                 |
| Depth                         | 3 1/16"                                          | 3 1/16"                                                  |
| Weight (approximate)          | 16 lbs                                           | 32 lbs                                                   |
| Certifications                | UL special locking arrangement, UL10C, cUL, CSFM |                                                          |
| Temperature                   | 0° to 49°C (32° to 120° F)                       | 0° to 49°C (32° to 120° F)                               |
| Wire gauge                    | 14-22 AWG                                        | 14-22 AWG                                                |

## Filler plates

| Length         | 12 1/2"   |
|----------------|-----------|
| Width x Height | Plate no. |
| 1 1/4" x 1/8"  | 4901F     |
| 1 1/4" x 1/4"  | 4902F     |
| 1 1/4" x 3/8"  | 4903F     |
| 1 1/4" x 1/2"  | 4904F     |
| 1 1/4" x 5/8"  | 4905F     |
| 3/4" x 1/2"    | 4906F     |
| 3/4" x 5/8"    | 4907F     |
| 3/4" x 3/4"    | 4908F     |

## Angle brackets

| Length          | 12 1/2"     |
|-----------------|-------------|
| Width x Height  | Bracket no. |
| 1" x 1"         | 4901A       |
| 1 1/2" x 1"     | 4902A       |
| 1 1/2" x 1 1/2" | 4903A       |
| 1 1/2" x 2"     | 4904A       |
| 1 1/2" x 2 1/2" | 4905A       |

Allegion, the Allegion logo, Schlage, and the Schlage logo are trademarks of Allegion plc, its subsidiaries and/or affiliates in the United States and other countries. All other trademarks are the property of their respective owners.

## About Allegion

Allegion (NYSE: ALLE) is a global pioneer in safety and security, with leading brands like CISA®, Interflex®, LCN®, Schlage® and Von Duprin®. Focusing on security around the door and adjacent areas, Allegion produces a range of solutions for homes, businesses, schools and other institutions. Allegion is a \$2 billion company, with products sold in almost 130 countries. For more, visit [www.allegion.com](http://www.allegion.com).