

PRODUCT FEATURES

- No cutting or altering of the jamb required
- Fail secure
- Releases under preload
- Fits standard ANSI 4–7/8" strike cutout
- Motorized, no solenoids
- Fully concealed installation
- Maintains dead latch function at all times
- Continuous duty
- Latch status sensor is standard
- One model works with most North American Mortise Locks (Sargent 7800 and 8200 require tab kit model #STK-1 for retrofit installations)
- MagnaCare[®] lifetime replacement, no fault warranty

PRODUCT OPTIONS

- 12 VDC
- 24 VDC
- FSUNL for field-selectable
 fail safe operation

SPECIFICATIONS

- UL10C Listed
- CAN4-S104, CAN/ULC Listed
- ANSI/BHMA A156.31, Grade 1; E09321, E09322, E09323
- NFPA-252 fire door compliant
- ASTM-E152 fire door compliant
- UL listed to ANSI/ SDI-BHMA A250.13 (60 PSI) Windstorm
- Patents: 6,022,056; 6,581,991; 6,902,214

Holding Force: 1500 lbs [680kg] static

Current Draw: 12 VDC-40 mA continuous, minimum 700 mA when operating

24 VDC-40 mA continuous, minimum 500 mA when operating

Higher capacity supply (1-4As) is recommended for startup inrush to achieve best operation under pre-load

Operating Temperature: -20 to +125F [-29 to +52C]

Shipping Weight: 2 lbs [0.91kg]

Finishes: US32D/630 - Satin Stainless Steel US10B/613 - Oil Rubbed Bronze

US03/605 - Polished Brass

LIFE

MAGNACARE WARRANTY


LISTED

MUNL Mortise UnLatch[®] Strike

Windstorm-Rated, Preload-Handling Strike for Mortise Locksets

Mortise UnLatch is for any application where an electric strike would be used for a mortise type lock. The Mortise UnLatch includes field adjustability for latch and deadlatch positions, releases under pressure and includes a latch status monitoring output.

>> MODELS		PART # Description	
MUNL-12	Mortise Unlatch - 12 VD	C, Satin Stainless Steel	
MUNL-12-US3	Mortise Unlatch - 12 VDC, Polished Brass		
MUNL-12-10B	Mortise Unlatch - 12 VD	C, Oil Rubbed Bronze	
MUNL-24	Mortise Unlatch - 24 VI	OC, atin Stainless Steel	
MUNL-24-US3	Mortise Unlatch - 24 VI	OC, Polished Brass	
MUNL-24-10B	Mortise Unlatch - 24 VI	OC, Oil Rubbed Bronze	





POWER TRANSFE



		x	5
	ï	T	i
	Ę	I	2
	¢		>



SECURITRON.COM

FIRE RATED

GRADF 1

JECURITRON

ASSA ABLOY

47

SPECIAL LOCKS

DURABLE