

Heavy Duty Pull Plates



1010-3



1015-3



1017-3

The Trimco's **Heavy Duty Pull Plates** combine the 1001 Series Push Plate with a large offering of different grip styles. These ADA compliant pull plates are available in 3"x12", 3-1/2"x15" and 4"x16" standard plate sizes and are mated with your choice of cast traditional or tapered pulls, half-round, 3/4 round, full round or bent bar type pulls. Custom plate sizes and finishes are also available.

APPLICATIONS

- Retail & Strip Malls
- Commercial & Industrial Buildings
- Multifamily & Mixed-Use
- Government & Military Facilities
- Public Buildings & Facilities

PULL PLATES

PRODUCT FEATURES

- Combines 1001 Series Plate with a wide range of grips.
- Plates are made of heavy duty .050" stainless steel, brass, or bronze and are heavy beveled on all four sides.
- Standard plate sizes include 3"x12", 3-1/2"x15" and 4"x16". Custom sizes and finishes also available.
- Available in a wide range of architectural materials and finishes including anti-microbial copper alloys.

SPECIFICATIONS

STANDARDS

BHMA J405



ANSI A117.1
Accessibility Code
(ADA Compliant)

SERIES

1010	Cast Traditional Pull
1012	Cast Tapered Pull
1013	3/4" Round Pull
1014	Half-Round Pull
1015	Bar Pull
1017	3/4" Dia. Round Pull
1018	1" Dia. Round Pull

MATERIAL OPTIONS

BR – Brass
BZ – Bronze
PL – Chrome Plated Brass or Bronze Castings
AI – Aluminum
SS – Stainless Steel
CU* – Copper Alloy

WARRANTY

Limited Lifetime Warranty

FINISHES

605	Polished Brass
606	Satin Brass, Dull
612	Satin Bronze
613	Oil Rubbed Bronze
625	Polished Chrome
626	Satin Chrome
628	Satin Aluminum, Clear Anodized
629	Polished Stainless Steel
630	Satin Stainless Steel
706	Sterose Copper (rose)
710	Steralloy Copper (silver)
SPEC	Special Options Available

Heavy Duty Pull Plates

HOW TO SPECIFY & ORDER

CHOOSE THE FOLLOWING

Series	Pull Type	Pull Plate Part #	Pull CTC	Plate Dimensions	Plate Thickness	Finishes	Options
1010	Cast Traditional Pull	1010-1	5"	3" x 12"	.050"	605 Polished Brass	• Cut-Cyl Cut for Cylinder • Cylt Cut for T-Turn • FR Full Round • RC Round Corners • Adhesive Tape Mounted
		1010-2	5"	3-1/2" x 15"		606 Satin Brass	
		1010-3	5"	4" x 16"		612 Satin Bronze	
1012	Cast Tapered Pull	1012-2	5-1/2"	3-1/2" x 15"		613 Oil Rubbed Bronze	
		1012-3	5-1/2"	4" x 16"		625 Polished Chrome	
1013	¾ Round Pull	1013-2	5-1/2"	3-1/2" x 15"		626 Satin Chrome	
		1013-2B	8"	3-1/2" x 15"		628 Satin Aluminum, Clear Anodized	
		1013-3	5-1/2"	4" x 16"		629 Polished Stainless Steel	
		1013-3B	8"	4" x 16"		630 Satin Stainless Steel	
						706 Sterose Copper (Rose)	
1014	Half-Round Pull	1014-2	6"	3-1/2" x 15"		710 Steralloy Copper (Silver)	SPEC Special Options Available
		1014-2B	8"	3-1/2" x 15"			
		1014-3	6"	4" x 16"			
		1014-3B	8"	4" x 16"			
1015	Bar Pull	1015-2	6"	3-1/2" x 15"			
		1015-2B	8"	3-1/2" x 15"			
		1015-3	6"	4" x 16"			
		1015-3B	8"	4" x 16"			
1017	¾" Dia. Round Pull	1017-2	6"	3-1/2" x 15"			
		1017-2B	8"	3-1/2" x 15"			
		1017-3	6"	4" x 16"			
		1017-3B	8"	4" x 16"			
		1017-3C	10"	4" x 16"			
1018	1" Dia. Round Pull	1018-2	8"	3-1/2" x 15"			
		1018-2B	10"	3-1/2" x 15"			
		1018-3	8"	4" x 16"			
		1018-3B	10"	4" x 16"			

EXAMPLE

For an 8" CTC stainless steel 1" Dia. Round Pull mated with a 4" x 16" .050" thick plate, specify or order: **1018-3.626**

1010



1012



1013



1014




1015



1017



1018



* Dimensions are informational only. Templates are available at www.trimcobbw.com