

Single Color Print Ribbons

- Solid color ribbons for printing a single color onto a label
- Can be swapped out for printing multi-color labels on BBP35 or BBP37 printer if a paneled multi-color ribbon is not on-hand

Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
BBP30, 31, 33, 35, 37	B30-R10000	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R6000	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R6200	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R6400	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R6600	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R4300	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-WT	White	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R4400-WT	White	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R6700-WT	White*	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R4500-SV	Silver*	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-RD	Red	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-GN	Green	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-BL	Blue	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-YL	Yellow**	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-YL2	Yellow**	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-OR	Orange	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-MA	Magenta	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-PRCCY	Process Cyan***	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-PRCYEL	Process Yellow***	4.330 (109.9)	200 ft. (60.9 m)
BBP30, 31, 33, 35, 37	B30-R10000-PRCMAG	Process Magenta***	4.330 (109.9)	200 ft. (60.9 m)



* B30-R4500-SV ribbon for use with B-342 black PermaSleeves® only; B30-R6700-WT ribbon for use with B-345 black PermaSleeves® only.

** B30-R10000-YL for printing yellow onto white. B30-R10000-YL2 for printing yellow onto other colors of B-595.

*** Process ribbons print a much lighter shade - designed to be used together with other process ribbons and black ribbon to lay down a dot pattern for printing "blended" colors and process color objects with the BBP35 or BBP37 printers.

BBP®35 & BBP®37 Multi-Color "Paneled" Print Ribbons

- Ribbons have panels of 2- or 4-different colors for printing multiple colors onto a label
- Use CMYK ribbon for printing blended colors. Blended colors are not as saturated as solid or spot color paneled ribbons, but do offer a broader palette of available colors and shades
- Print multiple colors without having to swap in multiple ribbons

Two Color Print Ribbons

Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
8" panel length - Typical yield: 100 panel sets per roll				
BBP35, 37 Only	B30-R10000-KR-8	Black and Red	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KY-8	Black and Yellow	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KB-8	Black and Blue	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KO-8	Black and Orange	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KG-8	Black and Green	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-GR-8	Green and Red	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
16" panel length - Typical yield: 60 panel sets per roll				
BBP35, 37 Only	B30-R10000-KR-16	Black and Red	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KY-16	Black and Yellow	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KB-16	Black and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KO-16	Black and Orange	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KG-16	Black and Green	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-RB-16	Red and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)

Four Color Print Ribbons

Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
8" panel length - Typical yield: 50 panel sets per roll				
BBP35, 37 Only	B30-R10000-KRGB-8	Black, Red, Green and Blue	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KRYG-8	Black, Red, Yellow and Green	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KRYB-8	Black, Red, Yellow and Blue	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KRBO-8	Black, Red, Blue and Orange	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-CMYK-8	Process Cyan, Magenta, Yell, Blk	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
16" panel length - Typical yield: 30 panel sets per roll				
BBP35, 37 Only	B30-R10000-KRGB-16	Black, Red, Green and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-KRYB-16	Black, Red, Yellow and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP35, 37 Only	B30-R10000-CMYK-16	Black, Cyan, Magenta, Yellow **	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)

** Process ribbons print a much lighter shade - designed to be used together with other process ribbons and black ribbon to lay down a dot pattern for printing "blended" colors and process color objects.

