



Models TS-15 and TS-16

Pneumatic Time Delay Request to Exit Station

Specifications

- Switch mounted on narrow 1-3/4" wall plate
- Two sets of contacts, one N/O, one N/C, isolated
- Contacts rated 10A at 120 VDC
- Switch depth behind plate: 1-1/4"

Features

- 1/4" push button protected by guard ring, mounted on either narrow or single gang wall plate
- Labeled "PUSH TO EXIT"
- Adjustable time range 2 to 60 seconds
- Requires no external power
- Timer life: one million operations
- 10" color coded leads

Options

- Available with 302 stainless satin steel wall plate
- Available with 430 stainless steel wall plate
- Order TS-15 for narrow wall plate
- Order TS-16 for single gang wall plate
- Custom silkscreening is available

Certifications & Listings

- UL 294 listed

Models

TS-15

RTE Pneumatic Time Delay 1-3/4"
SS PL w/Guard UL Listed

TS-16

RTE Pneumatic Time Delay SS SG
PL w/Guard UL Listed

ALARMCONTROLS



ASSA ABLOY