

REMOTE STATION PLATES

Limited Lifetime Warranty

MODEL RP-9 Single Gang Wall Plate



- Satin stainless steel
- 1/4" red and green LED's
- Works on 12 or 24VDC
- Current 13mA on each LED
- Custom screening available

Model RP-9L

- 1/2" diameter LED's

MODEL RP-20 Single Gang Wall Plate



- Satin stainless steel
- "D" hole for ACE keyswitch
- Custom screening available

Model RP-21

- Double "D" hole for Medeco keyswitch

MODEL RP-26 Single Gang Wall Plate



- Satin stainless steel
- N/O red pushbutton with guard ring
- Contacts rated 0.75A
- Custom screening available

Model RP-26A

- N/C black pushbutton with guard ring

MODEL RP-28 Single Gang Wall Plate



- Satin stainless steel
- 1/4" diameter red LED
- Works on 12 or 24VDC
- Current draw 13mA
- Custom screening available

Model RP-28L

- 1/2" diameter LED

MODEL RP-31 Single Gang Wall Plate



- Satin stainless steel
- Four 1/4" diameter red LED's
- Works on 12 or 24VDC
- Current 13mA on each LED
- Custom screening available

Model RP-32

- Four, 1/4" green LED's

MODEL RP-44 Single Gang Wall Plate



- Satin stainless steel
- DPDT shunt switch
- Contacts rated 2A
- Custom screening available

Model RP-45

- Two DPDT shunt switches

MODEL MP-26



- Chrome plated brass
- N/O red pushbutton with guard ring
- Size: 1-1/4" W x 2-1/4" L
- Contacts rated 0.75A

Model MP-26A

- N/C black pushbutton with guard ring

MODEL MP-44



- Chrome plated brass
- DPDT shunt switch
- Alternate action switch
- Size: 1-1/4" W x 2-1/4" L
- Contacts rated 2A
- Pushbutton changes from black to orange when pushed

MODEL WP-4



- Weather-proof station
- Self-closing cover
- 1/4" red and green LED's
- Operates on 12/24VDC
- "D" hole for ACE keyswitch

Model WP-6

- Double "D" hole for Medeco lock