

# ELECTRONIC BUZZERS

*Limited Lifetime Warranty*

## PA-100 Piezo Buzzer



- Buzzer mounts in 3/4" diameter hole
- Sound level 85dB @ 3 feet
- Voltage range 6VDC to 28VDC
- 6" red and black leads

## PA-200 Piezo Chime



- Piezo chime mounts in 1-1/4" diameter hole
- Sound level 85dB @ 3 feet
- Voltage range 6VDC to 28VDC
- Current draw 95mA @ 12 VDC, 140mA @ 24VDC
- 6" red and black leads

## PA-300 Dual Tone Piezo Buzzer



- Continuous and pulsing tones
- Sound level 85dB @ 3 feet
- Buzzer mounts in 3/4" diameter hole
- Voltage range 6VDC to 28VDC
- 6" red, yellow and black leads

## MODEL SC628 Sonalet



- Buzzer mounts in 1-1/8" diameter hole
- Sound level 85dB @ 3 feet
- Voltage range 6 to 28VDC
- Current draw 3mA @ 6VDC, 18mA @ 28VDC
- Screw terminals

## MODEL LA32 Piezo Buzzer



- Buzzer mounts in 5/8" diameter hole
- Sound level 85dB @ 3 feet
- Operates on 12 /24 VAC or VDC
- Current draw 5mA @ 12 VDC, 7mA @ 28VDC
- 3 adjustments: slow, steady or fast

## MODEL TS-34 Piezo Buzzer Station



- Buzzer is mounted on single gang stainless steel plate
- Sound level 85dB @ 3 feet
- Operates on 6 to 28VDC
- Other standard plate finishes are available
- Custom screening is available

## MODEL TS-34N Narrow Buzzer Station



- Buzzer is mounted on 1-3/4" stainless steel plate
- Sound level 85dB @ 3 feet
- Operates on 6 to 28VDC
- Other plate finishes available
- Custom screening available

## MODEL TS-41 Buzzer Station



- Buzzer is mounted on single gang stainless steel plate
- Sound level 85dB @ 3 feet
- Operates on 6 to 28VDC
- Other plate finishes available
- Custom screening available

## MODEL TS-42 Buzzer Station



- Buzzer is mounted on single gang stainless steel plate
- Sound level 85dB @ 3 feet
- Operates on 12/24VAC or VDC
- 3 adjustments: slow, steady, and fast
- Custom screening available