

MODEL AES-100

BHMA Grade 1 Dual Voltage Electric Strike



Designed for heavy-duty applications, the all-in-one **AES-100** offers dual voltage and field selectable fail secure/fail safe operation. Deep latch cavity accommodates cylindrical locksets with a 5/8" to 3/4" throw in steel, wood or aluminum frames.

- BHMA Grade 1
- UL 1034 Burglary Resistant, 1500 lb. static strength
- Static strength 70 ft-lbs. Dynamic strength endurance rating 500,000 UL tested, 1,500,000 factory tested
- Strike depth 1-1/2"
- Field selectable, fail safe/fail secure
- Dual voltage 12/24 VAC or VDC, continuous duty operation on DC
- Fully reversible for right or left hand doors
- Mounting kit includes two 4-7/8" stainless steel face plates (one round corner and one square corner)
- Current draw 12 VAC 130mA, 24 VAC 70mA
- Current draw 12 VDC 210mA, 24 VDC 105mA
- 7-7/16" round corner strike plate available. Model number **STR00004**



Alarm Controls
19 Brandywine Drive
Deer Park, New York 11729
(800) 645-5538
www.alarmcontrols.com

ASSA ABLOY, the global leader
in door opening solutions