

Model 1200L

1200 lbs Single Magnetic Lock with Status LED

Specifications

- 1200 lbs holding force
- Magnet size: 10-1/2" L x 2-7/8" H x 1-1/2" W
- Armature size: 7-3/8" L x 2-3/8" H x 9/16" W
- Operates on 12 or 24 VDC, selectable
- Low current draw: 400 mA at 12 VDC, 200 mA at 24 VDC
- Operating temperature: +14 to +131F [-10 to +55C]

Features

- Instant release, no hysteresis
- Red status LED
- Self drilling TEC screws
- Built-in arc suppression
- E-Z mount system, no special tools required
- Non-aluminum parts are plated to resist corrosion

- Can be used with any access control system
- Limited lifetime warranty

Options

- Clear anodized (US28) finish standard
- Duranodic (US40) finish available
- Dress covers in polished chrome and brass are available

Certifications & Listings

- UL 10C fire rated
- CAN4-S104 (ULC-S104) fire door conformant
- ULC-S527 listed
- UL 864 listed





ASSA ABLOY, the global leader in door opening solutions

alarmcontrols.com • 800.645.5538

Models

1200L

1200 lbs Single Door Magnetic Lock with status LED. 12 or 24 VDC. UL 10C and Canadian UL Listed

1200LDURO

1200 lbs Single Door Magnetic Lock with status, LED, 12 or 24 VDC, US 40 Duranodic Finish, UL 10C and Canadian UL Listed