



Model KP-300

Mullion Mount Vandal-Resistant Weather-Proof Digital Keypad with Built-In Card Reader

Specifications

- Operates on 12 VDC nominal, 11-15 VDC, operating current 95 mA
- Output 1: capacity of 1000 user codes and /or cards
- Output 2: capacity of 100 user codes and/or cards
- Die cast metal keys with audible and visible key press
- IP65 housing
- Operating temperature: -4 to +158F [-20 to +70C]
- LEDs indicate keypad status
- Operate with card only, user code and card, or user code only
- Two programmable SPDT relay outputs
- 50 visitor codes, programmable for one time use or with time limit
- Fully programmable from the keypad
- Keys are backlit for visibility in dark areas
- Three year warranty

Features

- Supplied with 2 EM cards
- Built-in tamper switch, built-in buzzer
- Heavy die cast surface mount housing with brushed 302 stainless steel faceplate

Options

- Supplied with 2 EM Cards. Model EM-10 is a package of 10 additional cards

Models

KP-300

Mullion Mount Keypad with Card Reader

ALARMCONTROLS



ASSA ABLOY