



# Model PA-200

## Piezo Chime

### Specifications

- Sound level 85 dB at 3 ft
- Operating voltage 12 to 24 VDC
- Current draw 95 mA at 12 VDC, 140 mA at 24 VDC

### Features

- Piezo chime can be flange mounted

### Options

- Model RP-22A single gang stainless steel plate available for wall mounting

### Models

#### PA-200

Chime Tone, 85 dB at 3 Ft, 12 or 24 VDC, Mounts in 1" Hole

# ALARM CONTROLS



**ASSA ABLOY**