

MORTISE CYLINDER KEYSWITCH STATIONS

MODELS

						
Switch Type	1.75" Wide	1.75" Wide Green LED	1.75" Wide Green LED Red LED	Single Gang	Single Gang Green LED	Single Gang Green LED Red LED
SPDT Momentary Action	MCK-1	MCK-2	MCK-3	MCK-4*	MCK-5*	MCK-6*
SPDT Alternate Action	MCK-1-2	MCK-2-2	MCK-3-2	MCK-4-2*	MCK-5-2*	MCK-6-2*
DPDT Momentary Action	MCK-1-3	MCK-2-3	MCK-3-3	MCK-4-3*	MCK-5-3*	MCK-6-3*
DPDT Alternate Action	MCK-1-4	MCK-2-4	MCK-3-4	MCK-4-4*	MCK-5-4*	MCK-6-4*
Pneumatic Time Delay 2 to 45 Seconds	N/A	N/A	N/A	MCK-4-5*	MCK-5-5*	MCK-6-5*

* Weather-proof cover and surface mount back box available. Add "-WP" to model number for the weather-proof option.

SPECIFICATIONS

- Stainless Steel Plate accepts standard 1 1/8" Mortise Cylinders
- Depth behind plate is 1.25"
- Switches terminated in colored leads
- Switch contacts rated 4A @28VDC
- LEDs operate on 12 or 24 Volts AC or DC
- Tamper-proof and Slotted-Head screws provided
- Limited Lifetime Warranty
- **Mortise Cylinder Not Supplied.** Model CY-1 and CY-1A Mortise Cylinders sold separately
- Pneumatic switch models operating temperature range is +15°F to +120°F



ASSA ABLOY

Alarm Controls
 19 Brandywine Drive
 Deer Park, New York 11729
 (800) 645-5538
www.alarmcontrols.com

ASSA ABLOY, the global leader
 in door opening solutions