5800 SERIES ADAEZ® LOW ENERGY OPERATOR



ADAEZ PRO: MODELS 5831 (PUSH), 5811 (PULL)

- » No electrical power required
- » Moderate to high traffic, manual opening applications that occasionally require automatic operation
- » Regenerative Drive System charges an onboard battery pack
- The PRO model excels in applications where the traffic pattern allows for 80 door cycles per day, 25% of which are automatic and 75% of which are manual. The PRO requires no electrical connection, no permit, no inspection, no wiring, and no low voltage license. It installs like a manual door closer in less than 1 hour.

ADAEZ PRO PLUS: MODELS 5833 (PUSH), 5813 (PULL)

- » 24VDC powered continuous automatic use
- » Connects to ANY 24VDC power supply
- » Commercial applications requiring push-and-go, power close and electric lock interface
- » Ideal for openings requiring continuous automatic use or automatic use more than 25% of the time

ADAEZ PRO COMPLETE: MODEL 5845 (PUSH AND PULL)

- » Bundles all the configurations of the ADAEZ PRO and ADAEZ PRO PLUS models into one easy to stock package
- » Right or left hand doors
- » Push and pull side mounting hardware
- » Black and aluminum finish covers
- » Mounting hardware for virtually any door and frame
- » 24VDC plug-in transformer kit for continuous automatic use applications

FEATURES

- » Regenerative drive or continuous duty operation
- » Non-handed
- » 5° door opening
- » Push and pull side mounting
- » Push-and-Go (ADA1015P Kit must be connected)
- » Power Close (ADA1015P Kit must be connected)
- » Radio Frequency stainless steel push buttons
- » Integral RF receiver
- » Shock absorbing arm
- » 693T (black) and 689 (aluminum) covers
- » 24VDC input port
- » ADA1015P hardware kit
- » Built-in ON/OFF Switch
- » Auxiliary activation input port
- » Maximum door width 48"
- » Maximum door weight 250 lbs
- » Patented Auto-Tune feature ensures safety and compliance with A156.19 code
- » 2 year limited warranty

CERTIFICATIONS

- » ANSI/BHMA A156.19 certified
- » ETL tested to UL/cUL standard for automatic doors on fire & smoke barrier doors
- Complies with requirements for Americans with Disabilities Act (ADA)
- » UL10c 90-minute positive pressure fire rating
- » Manufactured in an ISO 9001 and ISO 14001 certified facility
- » Verified by GreenCircle to offer these energy savings as compared to similar products:
 - > 5800 Series ADAEZ® (plug-in) 91% efficiency
 - > 5800 Series ADAEZ® (wireless) 100% efficiency








KITS

ADAEZ PRO - MODELS 5831 x NPB (Push), 5811 x NPB (Pull)



Non-Handed Shown Push

Side Mounting Parallel Arm

Narrow Style Push Buttons With Wireless (RF) Transmitters

Square Style Push Buttons With Wireless (RF) Transmitters


OPTION:



Aluminum Dress Cover

Replaces Standard Black Cover Operator Frame/Arm Always Black Finish


ADAEZ PRO PLUS - MODELS 5833 x SQPB (Push), 5813 x SQPB (Pull)



OPTION:



ADAEZ PRO COMPLETE - MODELS 5845 x NPB (Push & Pull), 5845 x SQPB (Push & Pull), 5845 x WTO (Push & Pull)



Wave-to-Open Switch

HOW TO ORDER

58 X **NPB** X 693T **FIRST TWO DIGITS FOURTH DIGIT SUFFIX PRODUCT SERIES** 1 - ADAEZ PRO NPB Narrow Push Buttons 3 – ADAEZ PRO PLUS **SQPB Square Push Buttons Push Buttons Not** 5 - ADAEZ PRO COMPLETE LPB **THIRD DIGIT** Included 1 – Pull **WTO** Wave-to-Open 3 - Push Switches** 4 - Push and Pull

Description	Specify Designation
Black Textured	693T
Aluminum	689

		Function		Description				
ADAEZ KITS	Model Number	PUSH	PULL	Narrow Style Buttons	Square Style Buttons	Wave-to- Open Switch	1015 Hardwire Kit: 24VDC	Aluminum Dress Cover
PRO	5831 x NPB	•		•				0
	5811 x NPB		•	•				0
PRO	5833 x SQPB	•			•			0
	5813 x SQPB		•		•			0
PRO PLUS	5833 x NPB	•		•			•	0
	5813 x NPB		•	•			•	0
PRO PLUS	5833 x SQPB	•			•		•	0
	5813 x SQPB		•		•		•	0
PRO COMPLETE	5845 x NPB*	•	•	•			•	•
	5845 x SQPB*	•	•		•		•	•
	5845 x WTO*	•	•			•	•	•

Note: *5845 is shipped 693T x 689 finish
**Only available for ADAEZ PRO COMPLETE

Optional partsStandard parts

Norton®

ASSA ABLOY

ASSA ABLOY is the global leader in door opening solutions, dedicated to satisfying end-user needs for security, safety and convenience Since 1880, Norton door controls have been an integral part of schools, hospitals and businesses around the globe. When you need products and people that perform at the highest level, rely on Norton – From Open to Close.

Norton Door Controls | www.nortondoorcontrols.com

3000 Highway 74 East | Monroe, NC 28112 | Tel: 1-877-974-2255 | Fax: 1-800-338-0965

ASSA ABLOY Door Security Solutions Canada | www.assaabloy.ca

160 Four Valley Drive | Vaughan, Ontario, L4K 4T9 Canada | Tel: 800-461-3007 | Fax: 1-905-738-2478

Norton is a brand associated with Yale Security Inc., an ASSA ABLOY Group company. Copyright @ 2012–2017, Yale Security Inc. All rights reserved. Reproduction in whole or in part without the express written permission of Yale Security Inc. is prohibited.