

- During the construction phase in non restricted areas, disposable plastic cores can be used, eliminating use and distribution of the actual keys
- Once construction is near completion, the permanent keyed cores will be installed and the building secured; permanent keyed cores are ordered separately as 6300 Cores
- Disposable cores are available for Mortise, Exits and most cylindrical lock sets
- Operate with coin or flat screw driver
- · One piece design allows for easy installation
- To order separately: Use p/n 13-5177
- Mortise Sizes available: 60-42, 60-43, 60-44 & 60-46
- Available 6300 Mortise Cams on Pg 6
- Specify required Cam as a suffix: 60-44-105 cam
- For Standard Cam: No Suffix is required

64- Prefix Construction Keyed Large Format Interchangeable (Removable) Core Keyed

- The SARGENT 6400 interchangeable brass construction core enables doors to be locked during project construction period
- Using 6400 cores prevents keys for the permanent key system from becoming available during the construction process
- After construction is completed, the 6400 brass cores are removed and replaced with 6300 keyed-permanent interchangeable Cores
- A special control key releases the locking sleeve of the cylinder core allowing immediate removal of the core
- Construction cores are all keyed alike in one KA keyset
- Furnished with 6 keys and 1 control as standard
- · Plug face dimpled for easy identification
- Order as a 64- prefix with products
- Mortise Sizes available: 64-42, 64-43, 64-44 and
- Available 6300 Mortise Cams on
- Specify required Cam as a suffix: 64-44-105 cam
- · For Standard Cam: No Suffix is required
- For keyed temp core sold separately use catalog # 6400

6300 Permanent Large Format Interchangeable (Removable) Cores Cylinders

- SARGENT LFIC (Removable) Core Cylinders and Master Key Systems are available for a quick change of cylinders for increased security. It is not necessary to remove the lock from a door to rekey the opening
- Special "control" key is used to release a locking cam allowing immediate removal of the core
- Available for use in many SARGENT products (Exit Devices, Mortise locks, Bored locks and padlocks)
- LFIC Key Systems can also include conventional cylinders operated by the same Master/change keys when the 6300 quick change feature is not needed
- Can be master or grandmaster keyed
- 2 Change keys provided
- 6 pin standard
- 1 bitted available for field keying
- 1 bitted cylinders supplied with 2 key blanks, pins and springs in chambers in 3 and 4 only
- HA keyway will be supplied unless otherwise specified
- Wide variety of master key systems available
- Permanent (keyed Large Format Interchangeable) cores supplied with hardware unless specified otherwise
- Available in the following SARGENT keyway families: A, B, C, G, H, K, L, N, R, and V
- Also available in the following single key sections: CR and S
- Control key is 6272 CTL, ordered separately
- Finishes: 4, 15
- Ordering as a: 6300 LFIC Core x finish and give all keying information

65-6300 Unassembled Core Only

- Unassembled core for field rekeying. Includes Control Sleeve and two key blanks
- Springs and pins to be ordered separately (see Pages 14 &15)
- 65- Prefix Uncombinate Cores
- Finishes: 4, 15
- HA key way will be supplied standard, unless otherwise specified
- Order as: 65-6300 x finish x keyway (6 pin only)

6300 Series Parts Only

13-0795 Plug, Finishes: 4, 15 13-3424 Inner Shell & Slide Assy, Finishes: 4, 15 13-0796 Control Sleeve Plug retaining ring

Slide for Cylinders with a box around the word SARGENT 13-0797 (Mfg prior to 4/06)

Slide for Cylinders WITHOUT a box around the word SARGENT (Mfg after 3/06)

For pins, springs & keying kits see Pages 14 & 15

63-34 Rim Cylinder

- Housing: Solid brass
- Cap: Brass, bronze or stainless steel
- Furnished standard with No. 97 rosette and compression ring
- Includes the same tailpiece and screw hole pattern as the #34 cylinder
- Finishes: 3,4,9,15,10,10B,10BE,10BL,20D,32,32D
- Order as: 63-34 x Finish
- Also available: 60-34 & 64-34 Rim Cylinders

63-40 Series Mortise Cylinders **Standard & Hotel Function Cylinders**



- Cylinder: Solid brass 1-5/32" diameter
- Cap: Brass, bronze and stainless steel
- Furnished standard with No. 97 rosette and compression ring
- Optional Collars/Spacers available and ordered separately, refer to product catalogs for additional information
- HA Standard Keyway (Except Hotel)
- For use in Sargent 78/8250s hotel function only, "C" series keyway supplied standard, unless otherwise specified. Offered in 50-63-43 size only (1-3/8") with 115 cam only
- Hotel emergency key is 7269 EMK, ordered
- Order hotel cylinders as 50-63-43 or 50-60-43 which will include the 115 cam
- Other SARGENT keyways available
- Mortise Sizes available: 63-42, 63-43, 63-44
- Available 6300 Mortise Cams on Pg 6
- Specify required Cam as a suffix: 63-44-105 cam
- For Standard Cam: No Suffix is required
- Finishes: 3,4,9,15,10,10B,10BE,10BL,20D,32,32D
- Order as: 63-42 x Finish
- 60-42 same as above, but supplied with plastic disposable plastic core

63-40 Series Mortise Cylinder Sizes

Cylinder#	63-42	63-43	63-44	63-46
Length	1-1/4" (32mm)	1-3/8" (35mm)	1-1/2" (38mm)	1-3/4" (44mm)

436-1 Slide Block Kit

- Includes fixture and staking tool for use only with the (10)- 6300 Series Cylinders manufactured after March 2006 for the ease of top loading in the field
- The kit includes 100 each slides p/n 13-1341, Staking Block and staking tool
- Cylinders manufactured after March 2006 will not include the box around the SARGENT logo and can be used with this kit



Cores without a box around the word

"SARGENT"

Key Blanks/Key Sections, Bitting Lists

7 Pin

LC

LE

LF

LG

LJ

LK

LL

RA

RB

RC

RE

RF

RG

RJ

RK

RL

CA

CB

CC

CE

CF

CG

C

 CK

CL

CR

Cylinders and Components

6265

6270

6273

6275

CN

LA

LB

LC

LE

LF

LG

LJ

LK

LL

7275

7278

HΑ

HB

HC

HE

HF

HG

HJ

HK

HL

RA

RB

RC

RE

RF

RG

RJ

RK

RL

CA

CB

CC

CE

CF

CG

CJ

CK

CL

CR

Key Blank

265

270

273

275

275

U

R

LD

LH

LM

LDH

LDM

LHM

IN

RD

RH

RM

RDH

RDM

RHM

RN

CD

CH

CM

CDH

CHM

CN

S

LA

LB

LC

LE

LF

LG

LJ

LK

LL

RA

RB

RC

RE

RF

RG

RI

RK

RL

CA

CB

CC

CE

CF

CG

C

ĆĶ


CL

CR

6278

6 Pin

For Multiplex Masterkey Systems	
(L keyway family shown, others similar	r)



Multi Keyway Systems

System Stock Keyways

System Hotel Keyway (Furnished in Large Bow only)

System **Contract Master Key Systems** System Contract MasterKey Systems

SARCENT SARGENT

Standard 6 pin

Large Bow approximately 15% larger than standard bow. Provided for SARGENT "C" family as standard.

Single Keyway

- R Section *
- S Section
- U Section*
- **CR Section**
- * Cylinders ordered in either U or R single section only. Offered as 1 bitted for

BITTING LISTS

278

Paper bitting lists provided at no charge for factory corresponding keyed orders when requested at time of hardware order. An owners letter of authorization must be attached to all purchase orders Existing key system bittings lists also available contact key records for more information.

Sections

- field keying

Restricted Keyways: Restricted keyways are SARGENT (factory) controlled geographically to limit sales and prevent unauthorized key duplication.

For availability of restricted keyways and key sections, contact SARGENT Key Records Department.

Orders for restricted keyway systems, key blanks and cylinders, require a letter of authorization from the system owner.

90622:L 04/01/17