

Bored Locks

7 Line



The SARGENT 7 Line is a key-in-lever lock designed for standard duty commercial interior and exterior applications in public buildings, medical offices, hotels/motels and government facilities. Exceeds ANSI/BHMA A156.2 Grade 2 standards for cycling and durability.

Bored
Locks

Program	Options	Functions	Rose	Lever	Finishes
24-Hour	KD	28-7G04, 28-7G05, 28-7U15*, 28-7G37, 28-7U65*	L	L	26D
1-Week	1, 20, 30, 60, 70, KD, LC, SC	28-7G04, 28-7G05, 28-7U15*, 28-7G15-3*, 28-7G37, 28-7U65*, 7U93*, 7U94*		B, L, P	10B, 10BE, 26, 26D
2-Week					03, 04, 10, 10B, 10BE, 26, 26D

Cylinder Options

- 30 Lever to accept Schlage cylinders - no cylinder provided
- 60 Disposable Construction Core
- 70 Interchangeable Core Disposable Plug
- KD Keyed Different
- LC Less Cylinder
- SC Schlage "C" Keyway

Mechanical Options

- 1 for 1-3/8" thick door
- 20 for 2-3/8" Backset

Functions

- 28-7G04 Storeroom
- 28-7G05 Office
- 28-7U15* Passage
- 28-7G15-3* Exit or Twin Communicating
- 28-7G37 Classroom
- 28-7U65* Bathroom/Privacy
- 7U93* Single Lever Pulls
- 7U94* Double Lever Pulls

Finishes

- 03 Bright Brass
- 04 Dull Brass
- 10 Dull Bronze
- 10B Oxidized Dull Bronze
- 10BE Dark Oxidized Satin Bronze - Equivalent
- 26 Bright Chrome
- 26D Satin Chrome

B Lever



L Lever



P Lever



L Rose

(3-1/2" Diameter)



* Cylinder options are not available