

## Rockwood 555 - Lever Extension Flush Bolt



### Specifications:

#### MATERIAL:

Brass

#### FASTENERS:

8 ea. #8 x  $\frac{3}{4}$ " Flat Head Combo Screws

#### FEATURES:

- For Fire Rated Hollow Metal Swinging Doors measuring up to 4'w x 10'h rated up to and including 3 Hours
- Fits ANSI A115 door and frame preparation
- $\frac{3}{4}$ " bolt throw,  $\frac{3}{4}$ " rod backset
- 12" rod length (center of face to bolt end - retracted)
- 1  $\frac{1}{2}$ " adjustable bolt head

#### OPTIONS:

- Other size rods available are 18", 24", 36", 48"
- Extra long bolt head - 2  $\frac{1}{2}$ " (or to your specification)
- Use #570 Dust Proof Strike to prevent dirt blocking bottom strike



### Available Finishes:

- US3/605
- US4/606
- US10/612
- US10B/613
- US10BE/613E
- US26/625
- US26D/626

#### SIZE:

Face Plate: 1" x 6  $\frac{3}{4}$ "

Strike:  $\frac{15}{16}$ " x 2  $\frac{1}{4}$ "

Guide: 1" x 2"

#### WEIGHT:

1.5 lbs./2

#### ANSI A156.16:

L04251