

The global leader in
door opening solutions

Rockwood 585-12 - 12" Surface Bolt



Available Finishes:

- US26D/626

SIZE:

Bolt Throw: 1 1/4"

Bolt Material: 3/4" x 3/4"

Bolt Length: 12"

WEIGHT:

3.9 lbs.

ANSI A156.16:

L04161

Specifications:

MATERIAL:

Steel

FASTENERS:

Bolt: 4 ea. 1/4"-20 x 2 1/4" Flat Head Machine Screws; 4 ea. 1/4"-20 x 1 5/8" Sex Bolts

Strikes: 2 ea. #14 x 2 1/2" Flat Head Sheet Metal Screws, 2 ea. Plastic Anchors;

2 ea. 1/4"-20 x 1" Flat Head Machine Screws, 2 ea. 1/4"-20 Lead Anchors

FEATURES:

- UL listed for use on inactive leaf of a pair of 3-hour labeled fire doors
- Includes a universal top strike and a mortise bottom strike
- Locks in both the up and down position
- Bolt locks automatically when thrown; can be released only by pressing knob toward door while retracting
- Can be used on any type of door
- Accommodates padlock



300 Main Street

Rockwood, Pennsylvania 15557

P: 800.458.2424 • F: 800.922.9212

www.rockwoodmfg.com • orders.rockwood@assaabloy.com

Copyright © 2017, Rockwood Manufacturing Company, an ASSA ABLOY Group company. All rights reserved. Reproduction in whole or in part without the express written permission of Rockwood Manufacturing Company is prohibited.