

DP4 Power Distribution Module

Description

Altronix DP4 Power Distribution Module conveniently converts a single AC/DC input into four (4) individual fuse protected outputs.



DP4

Specifications

Input

Voltage Handles up to 48VAC/VDC.

Output

Four (4) fuse protected outputs.
Outputs are rated @ 3.5A.
Surge suppression.

Indicators (LED)

Input Input voltage is present.

Physical and Environmental

Dimensions (L x W x H)

3.25" x 3" x 0.75" (82.55mm x 76.2mm x 19.5mm).

Product Weight 0.2 lbs. (0.09 kg).

Shipping Weight 0.3 lbs. (0.14 kg).

Temperature

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

Accessories:



ST3

ST3 - Snap Track (included)

Designed for mounting Altronix products to Din Rail without the use of mounting screws.



D10

D10 - Din Rail (order separately)

10" metal rail for mounting circuit boards and/or power supplies and peripherals inside equipment racks or enclosures.