




## BRUTE AND SUPER BRUTE

## SQUARE DOOR FLOOR SAFES

All BRUTE SERIES safes are designed to provide secure storage for documents, jewelry, precious metals and miscellaneous valuables at an economical price. When properly installed in a concrete floor, BRUTE SERIES safes provide excellent fire and burglary protection. BRUTE floor safes meet and exceed the requirements of the Insurance Offices Manual of Burglary Insurance. You may also add many options to customize your safe such as: A drop slot in the door, depository chute, digital keypad lock and keylocking dial to name a few. BRUTE SERIES safes may be installed in the floor, wall, cladding or within a larger safe.



- A handle activated locking mechanism consisting of three 1" diameter locking bolts. Each one is drive resistant, chromed steel with a long throw.
- One piece heavy duty dead bar behind hinge prevents removal of door even if hinges are removed during a forced entry attempt.
- Door is designed to fit full body size, which greatly reduces any possible pry points.
- Doors are interchangeable within product group.

## BODY:


- Oversize floor plate ensures strong installation in concrete.
- Flush cover plate.
- Solid steel hinge mechanism using  $\frac{3}{8}$ " diameter steel hinge pins and internal mounting bolts.

## SUPER BRUTE SERIES

## ADDITIONAL FEATURES:

- The **SUPER BRUTE's** new door jamb design is manufactured with state-of-the-art equipment, with built-in devices offering the ultimate protection against sledgehammer attack.
- "B+" rate door:  $\frac{3}{4}$ " **solid steel plate door** is standard.
- Doors are removable and interchangeable.

- A large, convenient  $10\frac{3}{4}$ " x  $11\frac{1}{8}$ " door opening for bulky items.
- One sliding shelf with double wide model (B3700). Two sliding shelves with triple wide models (B5800).
- Attractive carpeted floor in every unit.



DOUBLE COMPARTMENT

## SUPER BRUTE &amp; BRUTE

## STANDARD FEATURES:

- Black textured body and door.
- Attractive design offers strong reliable welds to protect against burglary attacks and reduce possible leakage.
- Every Brute Series safe now comes standard with AMSEC's ESL5 Electronic Lock with Illuminated Keypad in Bright Chrome. Optional combo lock available.
- An additional spring-loaded reloading device, activated by a punching attack.
- Lock and relocks are protected by a large carburized hardplate.

## BRUTE RECTANGULAR BODY, WIDE DOOR

## ADDITIONAL FEATURES:

- A large, convenient  $11\frac{3}{4}$ " x 16" door opening, for large bulky items or cash tray storage.
- B-rate door of  $\frac{1}{2}$ " solid steel plate.

## Super Brute Floor Safes

## Lifetime Replacement Warranty

For more information visit our website at: <http://www.amsecusa.com/floor-safes/brute/>

## SuperBrute "B" Rate Rectangular Hinged Door Floor Safes

Model	Inside Dimension H x W x D	Outside Dimension H x W x D	Clear Door H x W	Cu. In. Capacity	Wt.
B1500E5 *	12-1/4 x 13-1/4 x 8-3/4	12-3/4 x 14-1/8 x 11-3/4	10-3/4 x 11-1/8	1377	102
B2200E5 *	12-1/4 x 13-1/4 x 14	12-3/4 x 14-1/8 x 17 $\frac{1}{2}$	10-3/4 x 11-1/8	2203	118
B2900E5 *	12-1/4 x 13-1/4 x 18-1/4	12-3/4 x 14-1/8 x 21-3/8	10-3/4 x 11-1/8	2872	134
B3800E5 *	12-1/4 x 18 x 17	12-3/4 x 18-3/4 x 21-3/8	10-3/4 x 11-1/8	3864	136
B3700E5 *	12-1/4 x 23 x 14	12-3/4 x 24 x 17 $\frac{1}{2}$	10-3/4 x 11-1/8	3785	145
B5800E5 *	12-1/4 x 35 x 14	12-3/4 x 36 x 16-3/4	10-3/4 x 11-1/8	5758	185

\*Constructed of 3/4" door and B-Rate body. For Slotted door, see page 38. Slotted outer door not recommended for use on B1500.

## Brute Wide Door "B" Rate Rectangular Hinged Door Floor Safes

Model	Inside Dimension H x W x D	Outside Dimension H x W x D	Clear Door H x W	Cu. In. Capacity	Wt.
B1806	12-1/4 x 18 $\frac{1}{2}$ x 6	13-1/4 x 19 $\frac{1}{2}$ x 9	11-3/4 x 16	1360	102
B1810	12 $\frac{1}{2}$ x 18 $\frac{1}{2}$ x 10	13-1/4 x 19 $\frac{1}{2}$ x 13	11-3/4 x 16	2281	116
B1816	12-1/4 x 18 $\frac{1}{2}$ x 16	13-1/4 x 19 $\frac{1}{2}$ x 19	11-3/4 x 16	3626	142
B1816D *	12-1/4 x 18 $\frac{1}{2}$ x 5-3/4 (top) 12-1/4 x 18 $\frac{1}{2}$ x 10 (btm)	13-1/4 x 19 $\frac{1}{2}$ x 19	11-3/4 x 16 (top) 6-3/8 DIA (btm)	1303 (top) 2266 (btm)	152

\*Double Compartment - Slotted inner door. Slotted door not recommended for use on B1806.