



TF SERIES - THIRTY MINUTE FIRE

GUN SAFES



TF5924E5



TF5517E5

TF5924E5

SECURITY

- 3/16"-Thick Steel Plate Door
- Four-Way Bolt Work
- 14-Gauge Steel Body
- (14) 1 1/4" Chrome Plated Bolts
- 4 Pre-Cut Anchor Holes

FIRE PROTECTION

- Lined with Two Layers of Drywall on the Ceiling and Door
- Lined with One Layer of Drywall in All the Walls
- 30-Minute Fire Protection
- Dual Door Seals to Protect Against Fire and Smoke

FUNCTIONALITY

- U.L. Listed ESL5 Electronic Lock with Illuminated Keypad
- Industry's Most Flexible Interior
- Door Organizer
- Storage for One Long Gun or One Assault Rifle on the Door
- One electrical access hole



TF5517E5

SECURITY

- 3/16"-Thick Steel Plate Door
- Four-Way Bolt Work
- 14-Gauge Steel Body
- (8) 1" Chrome Plated Bolts
- 4 Pre-Cut Anchor Holes

FIRE PROTECTION

- Lined with Two Layers of Drywall on the Ceiling and Door
- Lined with One Layer of Drywall in All the Walls
- 30-Minute Fire Protection
- Dual Door Seals to Protect Against Fire and Smoke

FUNCTIONALITY

- U.L. Listed ESL5 Electronic Lock with Illuminated Keypad
- Industry's Most Flexible Interior
- Door Organizer
- One electrical access hole




Model	Outside Dimension H x W x D	Thickness (Inches)		Interior Capacity	Wt. Lbs.
		Door Overall / Steel plate	Body		
TF5924E5	59" x 24" x 18"	3 5/8" / 3/16"	14 ga	8-8-16 Gun + 1 Gun	388
TF5517E5	55-1/4" x 17-3/4" x 16"	3 1/4" / 3/16"	14 ga	11 Gun	286


Dimensions listed are exterior dimensions.
Add 2" to overall depth for lock and handle.

EXTERIOR COLOR:

Black (BK)



8-8-16
GUN INTERIOR
TF5924E5



11
GUN INTERIOR
TF5517E5