

Product data sheet

Characteristics

AR3305

NetShelter SX 45U 600mm Wide x 1200mm Deep Enclosure with Sides Black



Overview

Model Name	NetShelter SX 45U 600mm Wide x 1200mm Deep Enclosure with Sides Black
Includes	Baying hardware , Key(s) , Keyed-alike doors and side panels , Leveling feet , Mounting Hardware , Pre-installed casters , Side Panels
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Anguilla , Antigua And Barbuda , Argentina , Aruba , Australia , Bahamas , Bangladesh , Barbados , Belize , Bermuda , Bhutan , Bolivia , Brazil , Brunei Darussalam , Cambodia , Canada , Cayman Islands , Chile , Colombia , Cook Islands , Costa Rica , Cuba , Dominica , Dominican Republic , East Timor , Ecuador , El Salvador , Falkland Islands (Malvinas) , Fiji , Grenada , Guatemala , Guyana , Haiti , Honduras , India , Indonesia , Jamaica , Japan , KOREA, REPUBLIC OF , Malaysia , Mexico , Myanmar , Nepal , Netherlands Antilles , New Zealand , Nicaragua , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Singapore , Sri Lanka , Thailand , Trinidad And Tobago , United States , Uruguay , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES)

Supported Hardware

Panel Size	0
Brightness	0 nits
Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

Physical

Net Weight	310.2 lbs (141.0 kg) (141.0 kg)
Maximum Height	83.62 inches (2124.0 mm) (2124.0 mm)
Maximum Width	23.62 inches (600.0 mm)
Maximum Depth	47.24 inches (1200.0 mm) (1200.0 mm)
Shipping Weight	348.48 lbs (158.4 kg) (158.4 kg)
Shipping Height	88.19 inches (2240.0 mm) (2240.0 mm)
Shipping Width	29.37 inches (746.0 mm) (746.0 mm)
Shipping Depth	52.52 inches (1334.0 mm) (1334.0 mm)
Minimum Mounting Depth	7.52
Maximum Mounting Depth	41.26
Rack Height	45 U

Color	Black
Units per Pallet	1.0
Vertical Posts	16 gauge
Front Door	16 gauge
Rear Door	18 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge
Side Panels	18 gauge

Environmental

CFM	0
-----	---

Conformance

Approvals	UL 2416 , UL 60950-1
Standard warranty	5 year repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs