

AXIS P1265 Network Camera

Complete, extremely discreet HDTV 1080p pinhole camera

AXIS P1265 Network Camera is a cost-effective complete modular pinhole camera with HDTV 1080p resolution, ideal for discreet indoor eye-level surveillance. It can be installed in tight places or flush-mounted in a wall, ceiling, or metal panel with only a small pinhole lens visible, suitable in, for example, ATMs or vending machines. Equipped with WDR – Forensic Capture, enables the camera to handle scenes with strong variations in light. AXIS P1265 comes with a mounting bracket and an 8 meter (26 feet) detachable cable.

- > [HDTV 1080p resolution](#)
- > [WDR – Forensic Capture](#)
- > [Pinhole lens with 91° horizontal field of view](#)
- > [Axis Zipstream](#)
- > [Power over Ethernet](#)



AXIS P1265 Network Camera

Camera		Sustainability	PVC free
Image sensor	1/2.9" (effective) progressive scan RGB CMOS	Memory	512 MB RAM, 256 MB Flash
Lens	Fixed iris, fixed focus, pinhole 3.7 mm, F2.5 Horizontal field of view: 91° Vertical field of view: 45°	Power	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 2 max 4.0 W, typical 2.5 W
Minimum illumination	Color: 0.27 lux	Connectors	Female RJ45 for 10BASE-T/100BASE-TX PoE RJ12 for sensor unit
Shutter time	1/32500 to 2 s	Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations, see www.axis.com
Video		Operating conditions	-20 °C to 50 °C (-4 °F to 122 °F) Humidity 10–85% RH (non-condensing)
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles Motion JPEG	Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Resolution	1080p	Approvals	EMC 55032 Class B, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, VCCI Class B, RCM AS/NZS CISPR 32, ICES-003 Class B, KCC KN32 Class B, KN35 Safety IEC/EN/UL 62368-1 Environment EN 50581, IEC 60529 IP3X, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-14, IEC 60068-2-78, IEC 60068-2-6, IEC 60068-2-27
Frame rate	25/30 fps (50/60 Hz)	Dimensions	AXIS P12 Mk II Main Unit: 16.5 x 46 x 109 mm (5/8 x 1 13/16 x 4 5/16 in) AXIS FA1125 Sensor Unit: 28 x 24 x 20 mm (1 1/8 x 15/16 x 13/16 in) Sensor unit cable: 8 m (26 ft)
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264	Weight	AXIS P12 Mk II Main Unit: 72 g (2.5 oz) AXIS FA1125 Sensor Unit: 12.2 g (0.43 oz) Sensor unit cable: 128 g (4.5 oz)
Image settings	Compression, color, brightness, sharpness, contrast, white balance, exposure value, exposure control, exposure zones, local contrast, rotation, corridor format, WDR - forensic capture, text and image overlay, privacy mask, mirroring of images	Included accessories	Installation Guide, Windows decoder 1-user license, AVHS Authentication key 8-m (26 ft) black cable, 1 pcs locking nut, AXIS F82A06 Angled Pinhole Mount
Network		Optional accessories	AXIS T8120 15 W Midspan 1-port AXIS T8129 PoE Extender Network cable coupler indoor slim AXIS Surveillance Cards AXIS F7315 Cable White 15 m AXIS F8204 Mounting Band AXIS F8211 Pinhole Trim Ring For more accessories, see www.axis.com
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized certificate management	Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/vms
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty
System integration		a. <i>This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (ey@cryptsoft.com).</i>	
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform (ACAP); specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF [®] Profile S and ONVIF [®] Profile G, specification at www.onvif.org	Environmental responsibility: www.axis.com/environmental-responsibility	
Analytics	Included AXIS Video Motion Detection, active tampering alarm Supported AXIS Cross Line Detection Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap		
Event triggers	Analytics Edge storage events		
Event actions	File upload: email, FTP, HTTP, HTTPS, network share Notification: email, HTTP, HTTPS and TCP Pre- and post-alarm video buffering Send SNMP trap, WDR mode		
Built-in installation aids	Pixel counter		
Data streaming	Event data		
General			
Casing	AXIS P12 Mk II Main Unit: Steel and plastic Sensor unit: Plastic, aluminum		