

AZPS4CH-UPS

4 Channel Power Supply / UPS

This is a quick and cost effective solution for supplying 4 cameras with power. 12-13.8 VDC

Adjustable voltage for longer cable runs. Power LED indicator light. 5 amp.

- LED indication lamp
- Built in PTC Fuse
- 4 Terminal Blocks
- Adjustable Voltage
- 4 CH
- Compact size
- Battery not included



Use with AZBLN217, AZBLN218, AZBLN219 Baluns

AZBLN217

Passive Video and Power Transceiver,

1CH, Voltage: 12V~50V (AC RMS/DC) 4.5A (AC RMS/DC). Power Input & Surge Protection LED Light, Video distance over 2250 ft, Power Distance dependent on input voltage and voltage drop. (PAIR)



Voltage Drop According to Cable Length (24AWG):

Transmission Distance	Transmission Voltage (12V DC, 0.5A)	Transmission Voltage (12V DC, 1A)	Transmission Voltage (12V DC, 1.5A)
50M / 160Ft	13.5V	15.5V	17.0V
100M / 320Ft	15.5V	18.5V	22.0V
150M / 500Ft	17.0V	22.0V	27.0V
200M / 650Ft	18.5V	25.5V	32.0V