



AZS103-XX Siren / Strobe

Size: 4.8x2.9x1.7"

Operating Voltage: 6-15VDC

Rated Voltage: 12VDC

Rated Current: 280mA

SPL DB/1M: 115

Tone: Dual Tone

Color: White

(-RD/-BL /-WH)



AZS80 -XX Strobe Light

Size: 3.94x2.95"

Operating Voltage: 12/24v

Mounting: Twin Screw Holes
Red, Blue, Orange, Clear



AZS100 Siren

Size: 1 Gang Wall Box

Operating Voltage: 6-14VDC

Rated Voltage: 12VDC

Rated Current: 110mA

SPL DB: 105db/1m@14V

Tone: Single Tone

Color: White