

# Grilles & Baffles



**PG8U**



**PG8W**



**SG8W**



**WB8**

*Note: Colors of speakers shown may not be accurate and should not be used for reference purposes.*

**Description** Bogen metal grilles protect and conceal recessed 8" ceiling speakers. They are shipped complete with the hardware needed to mount a speaker to the grille.  
Bogen's Wall Baffle, WB8, will house any Bogen 8" speaker. Hardware for mounting a speaker to the baffle included.

**Features GRILLES**

- Available in aluminum, bright white, or off-white finish
- Protects and conceals 8" speakers
- Constructed of metal or aluminum

**WALL BAFFLE**

- Constructed of 3/8" particle board with reinforced corners
- Sloping front panel (13.5 degrees) provides enhanced downward dispersion

## Technical Specifications

Models*	Material	Finish	Style	Dimensions	Quantity	Shipping Weight (carton)
PG8U	Steel	Bright-white Enamel	Low Profile	13" Dia.	20/carton	26 lb.
PG8W		Off-white Enamel				
SG8W		Bright-white Enamel	Low Profile‡		10/carton	14 lb.
WB8	3/8" Particle Board	Simulated Walnut	9-1/2" W x 9-1/2" H X 5-1/4" D X 3-1/4" D (at bottom)		4 /carton	10 lb.

\* Mounting hardware included    ‡ Features hidden speaker mounting studs

---

**Architect  
and Engineer  
Specifications**

**Ceiling Grilles**

(Use for **PG8U**) The ceiling speaker grille shall be a Bogen model PG8U steel grille, or equivalent, capable of protecting and concealing a recessed 8" cone-type loudspeaker. The diameter of the grille shall be 13" and it shall be low profile and finished in bright white semi-gloss enamel. Mounting hardware shall be included.

(Use for **PG8W**) The ceiling speaker grille shall be a Bogen model PG8W steel grille, or equivalent, capable of protecting and concealing a recessed 8" cone-type loudspeaker. The diameter of the grille shall be 13" and it shall be low profile and finished in off-white semi-gloss enamel. Mounting hardware shall be included.

(Use for **SG8W**) The ceiling speaker grille shall be a Bogen model SG8W steel grille, or equivalent, capable of protecting and concealing a recessed 8" cone-type loudspeaker. The diameter of the grille shall be 13", the speaker mounting studs shall be hidden, and the grille shall be low profile and finished in bright white semi-gloss enamel. Mounting hardware shall be included.

**WB8 Wall Baffle** The loudspeaker wall baffle shall be a Bogen model WB8, or equivalent, capable of housing an 8" cone-type loudspeaker and angled (13.5 degrees) for additional downward sound dispersion. The baffle shall be constructed of 3/8" particle board, glued and covered in simulated walnut vinyl. Glue blocks shall be used to reinforce all side corner joints. The speaker opening shall be covered with a black grille cloth. Hardware for mounting the speaker to the baffle shall be supplied. Overall dimensions shall be 9-1/2" W x 9-1/2" H x 5-1/4" D (top) x 3-1/4" D (bottom).

---

**BOGEN®**  
**COMMUNICATIONS, INC.**

50 Spring Street, Ramsey, NJ 07446, U.S.A.

Tel: 201-934-8500 • Fax: 201-934-9832

[www.bogen.com](http://www.bogen.com)