

COMPACT AMPLIFIER SERIES

CC-Series Compact Mixer-Amplifiers



The **CC-Series** consists of five compact mixer-amplifiers, each providing 40 watts of output power. The features available and number of inputs vary per model (see chart below). Each unit measures 2 rack spaces in height but only 8-1/4" wide, allowing 2 units to be placed side-by-side without requiring additional rack spaces.

Product Features:

- 40 watts of output power
- Total Inputs: 2 to 5 for external equipment (inputs vary per model, see chart below)
- 6th Input for Media Player on CC4052M and CC4062MBT
- 7th Input for Bluetooth on CC4062MBT
- Individual volume control for each Input
- Individual phantom power for MIC inputs
- Media player accepts SD card and USB thumb drive; button controls for playback, volume, and EQ (Models CC4052M and CC4062MBT)
- MOH output with 1W/8-ohm and 600-ohm transformer-balanced outputs (Models CC4052M and CC4062MBT only)
- MOH source selectable from Media Player or Input 4
- 2 levels of priority: TEL is 1st priority, Input 1 is 2nd priority
- Audio-activated & Defeatable muting
- Bass and treble controls
- Compatible with 70V, 25V, 4-ohm, and 8-ohm systems
- REC output
- Peak and signal indicators
- External 24V DC supply input
- Listed to UL Standard 60065 for US and Canada
- Optional rack mount adapter (RPK93) available for single and side-by-side configurations (sold separately)

Technical Specifications, Dimensions, and Weights can be found on Page 79

Model	Total Number of Inputs	Number of MIC/Line Inputs (balanced)	Number of AUX Inputs (unbalanced)	TEL Input	Media Player Built-in	EQ for Media Player	Bluetooth Capability	Audio-activated Muting Priority Levels	MOH Output	Product Weight
CC4021	2	1	1					1		11 lb.
CC4041	4	3	1					1		11 lb.
CC4052	5	3	1	1				2		11 lb.
CC4052M	6	3	1	1	1	●		2	●	11 lb.
CC4062MBT	7	3	1	1	1	●	●	2	●	11 lb.

Dimensions

8-1/4" W
x
3-1/2" H
x
10-3/8" D

Accessories

RPK93 Rack Mount Kit



CC4021



CC4041



CC4052



CC4052m



CC4062MBT

CC-Series Front & Rear Panels (CC4062MBT shown here)

**Media Player
(4052m/4062MBT)**
Plays MP3 files from
SD Card or
USB Memory Stick.

**Bass & Treble
Controls**
Separate controls
for Bass & Treble
adjustment.

**External DC
Supply Input**
Power unit from
external batteries
or power supply
connection.

**Speaker
Outputs**
Compatible
with 70V, 25V,
4-ohm/8-ohm
systems.

**Music-On-Hold Output
(4052m/4062MBT)**
1-watt/8-ohm or 1V/600-ohm
transformer-isolated output;
independent volume control
for MOH output level;
select program material from
Media Player or Input 4.

**TEL Input
(4052/4052m/
4062MBT)**
Mutes all other
inputs when active.



**Input Level
Controls**
Front-mounted,
provided for
each input.

**Bluetooth
(4062MBT)**
Illuminates
when Bluetooth
connection is
achieved.

**Peak
Indicator**
Illuminates
when peak
output level is
reached.

**Signal
Indicator**
Illuminates
when signal is
present at
any input.



**REC
Output**
Line-level
output of the
same program
material to the
speakers.

**Input 4,
Unbalanced AUX**
Provides a high-impedance
mono-summing
input; can be set as
program source for
MOH output; Muteable
by TEL Input or Input 1.

**Inputs 2 & 3,
Balanced MIC/Line
(4041/4052/4052m/
4062MBT)**
Select Line, MIC, or MIC
with Phantom Power;
muteable by TEL Input,
or Input 1.

**Input 1,
Balanced
MIC/Line
(4041/4052/4052m/
4062MBT)**
Select Line, MIC, or
MIC with Phantom
Power; muteable
by TEL Input.

**Mute
Send**
Enables/
disables
muting of
inputs by
Input 1.






PRODUCT ACCESSORIES

AMPLIFIERS

Model #	Accessory Description	Associated Model(s)	Dimensions	Prod. Wt.	Page #	Images
GSRVC	Remote Volume Control	Gold Seal Series Amps	2-3/4" W x 4-1/2" H x 1-3/8" D	2 oz.	41	      
GSTRC	Gold Seal Series Security Cover	Gold Seal Series Amps	14-3/4" W x 3-1/2" H x 1" D	5 oz.	41	
MA3	Module Adapter	D-Series, WMA, DPA Amps	Works with advanced modules	1 lb.	39	
PVMC	Power Vector Module Cover	V-Series Amps, M-Class, VMIX	1-1/2" W x 3-1/8" H x 3/8" D	1 oz.	38, 45, 48	
PVSC	Power Vector Security Cover	V-Series Amps, VMIX	15-1/2" W x 3-1/8" H x 1/2" D	2 oz.	38, 48	
RVCP	Remote Volume Control Panel	V- & WV-Series Amps, VMIX	1-3/4" W x 4" H	2 oz.	38, 40, 48	
TL100	1:1 Ratio Plug-In Transformer	BPA60/HTA125A/HTA250A	1" dia. x 1-1/4" D	1 oz.	46	
TL600	Plug-In: 600-ohm Transformer	BPA60/HTA125A/HTA250A	1" dia. x 1-1/4" D	1 oz.	46	



MOUNTING / RIGGING KITS

Model #	Accessory Description	Associated Model(s)	Dimensions	Prod. Wt.	Page #	Images
108-2120	Yoke Assembly	AMT-12	24-1/2" W x 12" H x 3" D	7 lb.	1	                                 
108-2150	Yoke Assembly	AMT-15	27-1/4" W x 13" H x 3" D	8 lb.	1	
109-2140	Rigging Beam Assembly	AMT Series	22" W x 3" H x 2" D	15 lb.	1	
109-2151	Rigging Kit	AMT Series	10" W x 1-1/2" H x 1/4" D	2 lb.	1	
ATS70GB	Tripod Speaker Stand	AMT Series, BP-Series	H: 50"-77"; Base dia.: 40"	6 lb.	1	
BBF	Back Box for Flush Mounting	WV-Series	14-1/2" W x 24-3/4" H x 3-7/8" D	12 lb.	40	
BBS	Back Box for Surface Mounting	WV-Series	16-1/4" W x 26-3/4" H x 3-7/8" D	16 lb.	40	
BC1	Beam Clamp	Horn Loudspeakers	2-1/8" W x 2" H x 3/4" D	6 oz.	13, 16, 26, 28	
CK10	Cable Kit (Silver)	HFCS1/OCS1/OPS1/HFSF1/CSUB/MPS1/MPS2	10 feet long	4 oz.	2, 6, 7	
CK10B	Cable Kit (Black)	OPS1B/MPS1B/MPS2B	10 feet long	4 oz.	2, 6	
CK10W	Cable Kit (Off-White)	OPS1W/MPS1W/MPS2W	10 feet long	4 oz.	2, 6	
GSRPK	Rack Kit	Gold Seal Series Amps	1-1/4" W x 3-1/2" H x 10-1/4" D	2 lb.	41	
HSES10	Horn Speaker Electrical Box Strap	Horn Speakers**	1/2" W x 5-1/2" long	3 oz.	13, 16, 28	
MR8	Mounting Ring	S86, S810, CS1EZ, ASWG1/DK	12" dia. x 3/4" D	15 lb.*	11, 16, 23	
RE84	Round Enclosure	S86, S810, CS1EZ, ASWG1/DK	12-1/4" dia. x 4-1/2" D	24 lb.*	11, 16, 23	
RK78	Rack Panel Kit	CDR1	19" W x 3-1/2" H x 7" D	3 lb.	57	
RMPWMK3	Remote Panel Mounting Kit	PM3180	9-1/8" W x 4-3/4" H x 3/4" D	2 lb.	47	
RPK35B	Rack Panel Kit	C10/C20/CAM2	19" W x 3-1/2" H x 6-1/2" D	3 lb.	42, 50	
RPK50	Rack Mount Kit	C35/C60/C100	2-1/2" W x 3-1/2" H x 2-1/8" D	10 oz.	42	
RPK53	Rack Mount Kit	BPA60	2" W x 3-1/2" H x 1" D	7 oz.	46	
RPK79	Rack Mount Kit	PM3180	1" W x 5-1/4" H x 3-1/2" D	14 oz.	47	
RPK82	Rack Mount Kit	TPU35B/60B/100B	3" W x 8-3/4" H	14 oz.	43	
RPK84	Rack Mount Kit	PCM2000	7" W x 8" H	2 lb.	35	
RPK86	Rear Rack Support Brackets	M-Class/Black Max Amplifiers	3-3/4" W x 3-1/2" H	7 oz.	44, 45	
RPK87	Rack Mount Kit	V-Series, VMIX	1" W x 3-1/2" H x 3-3/4" D	1 lb.	38, 48	
RPK88	Rack Mount Kit	PCM2000	19" W x 10-1/2" H x 2" D	3 lb.	35	
RPK89	Rack Mount Kit (Single)	UDR800	2 Pieces; 1 Rack Space	6 oz.	58	
RPK90	Rack Mount Kit (Double)	UDR800	3 Pieces; 1 Rack Space	4 oz.	58	
RPK91	Rack Mount Kit	TAMB2/TAMB2PS	2 Pieces; 1 Rack Space	7 oz.	32	
RPK93	Rack Mount Kit	CC-Series	1-1/4" W x 3-1/2" H x 8-1/4" D	2 lb.	37	
RPKUT11	Rack Mount Kit/Security Cover	UT11	19" W x 5-1/4" H x 2-3/8" D	2 lb.	31	
SMTB	Tile Bridge for Easy Install Speakers	ASM1, SM1EZ/SM4T	4-3/8" W x 1-1/4" H x 23-3/4" D	5 lb.*	15, 24	
TB8	Tile Bridge	S86, S810, CS1EZ, ASWG1/DK	23-3/4" W x 3/4" H x 14-1/2" D	17 lb.*	11, 16, 23	
TBCR	Tile Bridge Support Ring	HFCS1/OCS1	17" W x 1-1/8" H x 24" D	2 lb.	2, 6	
TBSF	Tile Bridge	HFSF1, SEC4T	10" W x 1/2" H x 24" D	14 oz.	7, 11	
TCSPT1	Terminal Cover for Conduit	Horn Speakers***	1-3/4" W x 3" H x 1-1/4" D	2 oz.	13, 16, 28	
TMA812	Tilt Mount Adapter	A12 & A8	7" W x 4-3/4" H x 4-1/2" D	2 lb.	5	
WMAD	Door for WV-Series Amps	WV-Series	16-1/4" W x 26-3/4" H x 1" D	9 lb.	40	
WMK1	Wall Mounting Kit	C10/C20/CAM2	14-1/2" W x 16" H x 4" D	10 lb.	42, 50	



*Weight based on per carton. Check with Bogen for quantity per carton.

**Horn Speakers: AH5A, AH15A, BDT30A, HS15EZ, HS30EZ, IH8A, KFLDS30T, SP158A, SP308A, SPT15A, & SPT30A.

***Horn Speakers: AH5A, AH15A, BDT30A, HS15EZ, HS30EZ, KFLDS30T, SP158A, SP308A, SPT15A, & SPT30A.