



Freestanding HomeSafe H3

SECURITY LEVEL A

- single walled home safe, compact - fits onto every shelf
- security level A according to VDMA 24992, 5/1995
- single walled body
- double-walled door
- effective square bolt locking

- prepared for double wall fixing, with fixing material, 2 drill holes at half height on the back wall
- ideal for A4 documents
- 2 keys included
- includes one shelf
- colour: black



H 3 S



Version S

Security safe lock 'SecuSafe', VdS tested, ECB-S certified according to EN 1300 class 1/A, with 2 keys, 9 levers, more than 1.000.000 key differs.

Art.-No.	EAN	Exterior H x W x D	Interior H x W x D	Door H x W	Weight	Volume
	40 03482...	mm	mm	Opening mm	kg	l
H 3 S	25000 6	257 x 347 x 298	216 x 340 x 243	184 x 276	16,0	17,8

Key blank for H 3 S

Key	EAN	
	40 03482...	
As per sample	16620 8	Length of key 68 mm
Key blank 51	16670 3	Key blank, PU 3 pcs.



H 3 E



Version E

Electronic combination lock 'SecuTronic', VdS tested, ECB-S certified according to EN 1300 class 2/B, 1.000.000 different combinations possible, incl. batteries. The locking armature protrudes 9 mm.

Art.-No.	EAN	Exterior H x W x D	Interior H x W x D	Door H x W	Weight	Volume
	40 03482...	mm	mm	Opening mm	kg	l
H 3 E	25020 4	257 x 347 x 298	216 x 340 x 243	184 x 276	16,0	17,8

Freestanding home safe HomeSafe H 3 with slot

- with slot 230 x 8 mm
- ideal for fast and safe storage of banknotes or envelopes
- light weight of 16 kg, makes this safe ideal for mobile use, for example, at events etc.
- colour: black
- technical features as per H 3 safes above

- **version S:**
Security safe lock - VdS tested;
ECB-S certified according to EN 1300 class A, 9 levers, more than 1.000.000 key differs
- **version E:**
Electronic combination lock 'SecuTronic', VdS tested;
ECB-S certified according to EN 1300 class 2/B.
1.000.000 different settings possible.
Incl. 3 batteries (Micro LR 03 AAA).
The locking armature protrudes 9 mm.



H 3 E C4 EWS

Art.-No.	EAN	Exterior H x W x D	Interior H x W x D	Door H x W	Weight	Volume
	40 03482...	mm	mm	Opening mm	kg	l
H 3 S C4 EWS	26090 6	257 x 347 x 298	216 x 340 x 243	184 x 276	16,0	17,8
H 3 E C4 EWS	26190 3	257 x 347 x 298	216 x 340 x 243	184 x 276	16,0	17,8

BURG-WÄCHTER Security-Level



LEVEL



LEVEL



LEVEL



LEVEL

