

QUADRA VIDEO EXT UNIT AND SWITCHING KIT. 2-WIRE**Main specifications**

Type:	Single-plate entrance panel
Type of finish:	Alluminio pressofuso
Audio/video system:	Yes
Wall-mounted:	Yes
Camera:	Color
Video encoding:	MPEG
Type of sensor:	1/4" CMOS
Horizontal resolution (TVL):	380
Minimum colour illumination (lux):	1
Lens size (mm):	2.1
Camera orientation:	Yes
Power supply:	Bus
Maximum current absorption (mA):	250
Clamps:	LL RTE COM DO SE- SE+C NC NO
Buttons to call:	Yes
Total buttons:	4
Microphone volume control:	Yes
Loudspeaker volume control:	Yes
Operating temperature (°C):	248.15 ÷ 328.15
IP protection rating:	IP54
Vandal Resistant rating (IK code):	IK08

Compatibility

Simplebus Top audio/video system:	Yes
-----------------------------------	-----