

Accessories

CRL JACKSON OVERHEAD CONCEALED CENTER HUNG DOOR CLOSERS

- Suitable for Doors From 30" to 48" (762 to 1219) Wide
- Five Year Limited Warranty
- UL Listed

Overhead Door Closers



ADJUSTABLE SPRING POWER OFFSET ARM PACKAGE



- Adjustable Spring Power Size 1 (Barrier-Free) to Size 4 (Regular)
- Meets A.D.A. Opening Force Requirements
- Available in Two Arm Finishes



ALUMINUM PART NO.	DARK BRONZE PART NO.	SPRING SIZE	TYPE
21201U62817	21201U31317	Adjustable	105° No Hold Open
21201U62818	21201U31318	Adjustable	105° Hold Open
21201U62819	21201U31319	Adjustable	90° No Hold Open
21201U62820	21201U31320	Adjustable	90° Hold Open

Minimum order: 1 each. All Door Closers can be combined for quantity pricing.

REGULAR SPRING POWER OFFSET ARM PACKAGE

- Fixed Spring Size
- Available in Two Arm Finishes



ALUMINUM PART NO.	DARK BRONZE PART NO.	SPRING SIZE	TYPE
21201U62801	21201U31301	Regular	105° No Hold Open
21201U62802	21201U31302	Regular	105° Hold Open
21201U62803	21201U31303	Regular	90° No Hold Open
21201U62804	21201U31304	Regular	90° Hold Open

Minimum order: 1 each. All Door Closers can be combined for quantity pricing.

CRL JACKSON OVERHEAD CONCEALED DOOR CLOSER BODIES

- Closer Body Only in Fixed and Adjustable Spring Sizes
- Suitable for Doors From 30" to 48" (762 to 1219) Wide



ADJUSTABLE SPRING POWER OVERHEAD CONCEALED DOOR CLOSER BODY

- Adjustable Spring Power Size 1 (Barrier-Free) to Size 4 (Regular)
- Can Retrofit Existing Fixed Spring Closers
- Five Year Limited Warranty



Body Only – Mounting Clips are not included. For standard clips, specify Part No. 20219.

1/2" STANDARD SPINDLE PART NO.	SPRING SIZE	TYPE
20101M17	Adjustable	105° No Hold Open
20101M18	Adjustable	105° Hold Open
20101M19	Adjustable	90° No Hold Open
20101M20	Adjustable	90° Hold Open

Minimum order: 1 each. All Door Closers can be combined for quantity pricing.

STANDARD OVERHEAD CONCEALED DOOR CLOSER BODY

- Fixed Regular Spring Size
- Five Year Limited Warranty



Body Only – Mounting Clips are not included. For standard clips, specify Part No. 20219.

1/2" STANDARD SPINDLE PART NO.	SPRING SIZE	TYPE
20101M01	Regular	105° No Hold Open
20101M02	Regular	105° Hold Open
20101M03	Regular	90° No Hold Open
20101M04	Regular	90° Hold Open

Minimum order: 1 each. All Door Closers can be combined for quantity pricing.

A.D.A. NOTE: Although the Adjustable Spring Power Door Closer can be adjusted to compensate for site conditions, adequate closing force might not be obtained while complying with A.D.A. opening force requirements.

Visit crlaurence.com for all available CRL Jackson door closer packages and accessories.

Online usalum.com By Phone (800) 262-5151
 Online crlaurence.com By Phone (800) 421-6144