















Dimensions

(unit: mm [inch])





Summary

The Blackjack® CUBE™ can record and manage up to 64 2.1MP Cameras at 30fps, 360Mbps throughput. The hardware includes DVI-D/DVI-I outputs, Windows7 OS, and Dual Network Card. The NVR is ONVIF conformant and is available with 3-18TB HDD and 5 Year Limited Warranty.

Features

- Supports All ONVIF Conformant IP Cameras
- Record up to 64 IP Cameras with Total Throughput up to 360Mbps
- · Storage options 3-18TB Internal Storage
- DVI-D or True HD video output
- Dual Network Ports
- USB Interface
- Windows 7[®] 64 Bit OS on Separate SSD
- Hosting DW Spectrum® IPVMS for Setup, Configuration, Monitoring and Recording
- One-time Recording License Charge, Fully Transferable Between Cameras and Encoders
- · No Annual Maintenance Fees
- Simple Enterprise Scalability
- Auto Device Discovery
- Dual Stream Recording
- 5 Year Limited Warranty

Available Models

- DW-BJCUBE3T 3TB Internal Storage.
- DW-BJCUBE4T 4TB Internal Storage.
- DW-BJCUBE6T 6TB Internal Storage.DW-BJCUBE9T 9TB Internal Storage.
- DW-BJCUBE12T 12TB Internal Storage.
- DW-BJCUBE18T 18TB Internal Storage.

Specifications



MODEL		BLACKJACK CUBE
Maximum IP Cameras		64
Included IP Licenses		4
Form Factor		Desktop
Operating System		Windows® 7 64 Bit
CPU		Intel [®] i5 [®] Processor
Memory		8GB
NIC		2x Gigabit Ethernet (RJ45)
System	Max Video Storage Rate (Mbps)	360 Mbps
Storage	Maximum Hard Drives	3 x SATA HDD
	Maximum Storage	18TB
Video-Out	Outputs	DVI-D or True HD Output
	Resolution	HD 1080p
Pre-Loaded VMS Software		DW Spectrum [®] IPVMS
Unlimited Remote Clients		Cross Platform - Windows®, Linux® and Mac®
Mobile Apps		iOS [®] and Andriod [®]
DW Spectrum [®] IP Video Management Software		"The Grid" flexible user interface with Unlimited layouts
		Seamless transition from live to recorded video
		Unique Interactive timeline with built in Smart, Thumbnail and Calender Search
KeyBoard & Mouse		Included
Power		300W**
Operating Temperature and Humidity		5~40 °C / 20~90% RH
Dimension (WxDxH) (inches)		12.8" x 8.5" x 7.5"
Warranty		5 Year Limited
* Δvailable at ti	me of initial order only /	** UPS Recommened

* Available at time of initial order only.

** UPS Recommended







