



6010



6020

## 6000 Series Monitor Panels

6000 Monitor Panels provide bi-color LED's, red/green, operating on 12 or 24 VDC. Mounted on brushed stainless steel US32D switch plate.

MODEL	PRODUCT	WEIGHT
<b>6010</b>	One Bi-Color LED, Red/Green, 12/24VDC	.2 Lbs.
<b>6020</b>	Two Bi-Color LED's, Red/Green, 12/24VDC	.3 Lbs.

## OPTIONS

<b>DBL-AUD</b>	Two Gang Plate with Audible Sounder - 1-28VDC.
<b>NR</b>	Narrow Plate - 1-3/4" wide, substitute.
<b>SF</b>	Special Finishes - Standard finish US32D. See page 52.



6115



6125

## 6000 Series Pushbuttons

6000 Series controls provide a popular selection of request to exit (REX) controls in multiple switching configurations. Monitoring is accomplished with optional illuminated or audible indicators. Standard finish - Brushed Stainless Steel US32D. Standard button color - Green. All switches SPDT contacts.



6135



6145

MODEL	PRODUCT	WEIGHT
<b>6115M</b>	One Pushbutton, 1 Gang, Momentary	.3 Lbs.
<b>6115A</b>	One Pushbutton, 1 Gang, Alternate Action	.3 Lbs.
<b>6125M</b>	Two Pushbuttons, 1 Gang, Momentary	.4 Lbs.
<b>6125A</b>	Two Pushbuttons, 1 Gang, Alternate Action	.4 Lbs.
<b>6135M</b>	Three Pushbuttons, 1 Gang, Momentary	.5 Lbs.
<b>6135A</b>	Three Pushbuttons, 1 Gang, Alternate Action	.5 Lbs.
<b>6145M</b>	Four Pushbuttons, 2 Gang, Momentary	.6 Lbs.
<b>6145A</b>	Four Pushbuttons, 2 Gang, Alternate Action	.6 Lbs.

## OPTIONS

<b>AUD</b>	Audible Sounder - 1-28VDC (Requires DBL option).
<b>DBL</b>	Two Gang Plate - 4-9/16" wide, for options.
<b>ILM</b>	Illuminated Pushbutton - Specify 12 or 24VDC (per button).
<b>LED</b>	Bi-Color LED - Red/Green, 12/24VDC.
<b>NR</b>	Narrow Plate - 1-3/4" wide, substitute.
<b>P2</b>	Additional set of SPDT contacts (per button).
<b>SF</b>	Special Finishes - See page 56.
<b>WPC</b>	Weather Proof Cover - For single gang 6115 only.
<b>ATS</b>	Anti-Tamper Switch