



**ELK-P624**



### 6, 12, or 24VDC Power Supply Board

Trouble-free, general-purpose power supply/charger ideal for alarm, access control, and CCTV applications. Features auto-resetting "fuseless" overload protection which eliminates costly service calls to replace blown fuses.

- Auto-Resetting "fuseless" overload protection
- Selectable 6, 12, or 24VDC Output
- Visual AC & DC Power Indicators
- Built-in Surge Suppression
- Battery Charging Circuit
- Size: 3"W x 3"H x 1"D
- **Lifetime Limited Warranty**
- Output Current:
  - 1.2 Amps @ 6V
  - 1 Amp @ 12V
  - .8 Amps @ 24V
- Input Transformer Requirements:
  - 6V operation: 12 VAC Transformer
  - 12V operation: 16.5 VAC (TRG1640)
  - 24V operation: 24 VAC (TRG2440)



**ELK-P212S**



### Supervised Remote Power Supply

The ELK-P212S is a Supervised Remote Power Supply / Battery Charger, providing 12 VDC output with up to 2 Amps of total current. It supervises the AC Power Input as well as the rechargeable Battery, and can report abnormal conditions back to an ELK-M1 Control over the RS-485 four (4) wire data bus. It also features relay outputs for AC and Low Battery to allow "stand-alone" operation with other controls.

- M1 Control allows:
  - Remote power reset of powered peripherals
  - Data-bus supervision of AC and Battery status
- Stand-alone flexibility
  - Two (2) sets of DC outputs
  - On-board relay to supervise battery status
  - On-board relay to supervise AC status
- Master AC and Battery ON / OFF Power Switch
- Visual AC Power Indicator
- AC Input: 16.5VAC, 45VA (TRG1640 or equiv.)
- DC Output Voltage: 13.8 Volts DC +/- 5%
- Current Rating: 2.0 Amps
- Wattage: 30 Watts
- DC Output Protection: Auto Resetting PTC
- Rechargeable Battery Size: Max. 12 Ah
- Low Battery Cutoff Threshold: ~10 Volts.
- Load Regulation: + / - 2%
- **Lifetime Limited Warranty**



**ELK-P1216**



### Plug-in Switching DC Power Supply

All purpose 12 Volt DC Plug-In Switching Power Supply ideal for alarm, access control, and CCTV applications. It plugs into a 120 Volt AC outlet and supplies 1.5 Amps of regulated 12VDC.

- Computer Grade Switching Power Supply
- Regulated 12VDC Output
- Slimline Design
- UL Listed
- RoHS Compliant
- Efficiency Level: V
- **Lifetime Limited Warranty**
- DC Output Voltage: 12 Volts DC
- Current Rating: 1.5 Amps
- Six foot cord and 2.1mm x 5.5mm x 9mm Power Plug (center positive)
- Color: Black
- Size: 3"H x 2"W x 1.75"D



**ELK-965**



### Low Battery Cutoff & Master Power Switch

Total power control for any 12V control panel or power supply. Disconnects battery if voltage falls below 10VDC as a result of extended AC power outage. Convenient On/Off switch for manual disconnect.

- Automatic Low Battery Cutoff Protects Battery From Deep Discharge
- Installer Friendly - Small Compact Size
- Includes AC Wires & Battery Leads
- **Lifetime Limited Warranty**
- Works with most 12 Volt DC Control Panels or power supplies
- AC Power Leads: 18 AWG, 18" Length
- Maximum Transformer Size: 18 VAC
- Battery Leads: 18 AWG, 18" Length
- Low Battery Cutoff Voltage: ~10VDC



**SAVE with 20  
Piece Bulk Packs  
ELK-965B20**



**Master Power Switch  
Only, 20 Piece Bulk Pack  
ELK-964B20**

