

Features:

High power handling 6.5" in-ceiling speaker system
New trimless magnetic grille
Single point stereo speaker (left + right channels)
Excellent coverage for hallways and smaller rooms
Smooth-wide frequency response
6.5 inch dual voice coil polypropylene woofer cone
Rubber woofer surround
20 oz ferrite woofer magnet
Dual 1 inch silk dome tweeters (Aim-able)
Articulated tweeter assembly (wide dispersion)
Neodymium tweeter magnets
PTZ tweeter protection (auto resetting)
Dual high quality crossovers
Air core inductors
4 heavy duty "Tough-Cam" mounting clamps.
Dual gold plated 12awg binding posts
Complete rough in bracket included (RI-675)
Paint able to match any decor
Sold as each
Master carton 2 pcs
10 year warranty



Specifications:

Diameter Woofer 6.5" (165.1mm)
Woofer type Polypropylene dual voice coil
Diameter Tweeter Dual 1" (25.4mm) silk dome aim-able
Articulated tweeter mount (15 degrees)
Power Handling 125 watts max
Impedance 8 ohms (nominal)
Frequency Response 40Hz - 20kHz (+/-10dB)
Dispersion 110
Sensitivity 92dB (1W 1M) Average

Included:

RI-675 rough-in bracket
Cutout template
Paint shield

Dimensions:

Dimensions Overall 10.125" (250mm)
Cutout Dimensions Speaker 8.25" (210mm)
Cutout Dimensions RI Bracket 8.5" (216mm)
Depth 3.5" (90mm)
Shipping Weight 14lbs (6.3kg) master carton 2 pcs
Shipping dimensions 14x12x13" master carton 2 pcs



New "Tough-Cam" Mounting System

