

Features:

Hi fidelity 4" surface mount speaker system
Suitable for indoor or outdoor use
Smooth-wide frequency response
Excellent fidelity for music or voice
4 inch polypropylene woofer cone
Rubber woofer surround
12 oz ported ferrite woofer magnet
1 inch silk dome tweeter
Neodymium tweeter magnet
PTZ tweeter protection with auto reset
High quality crossover with air core inductors
Aluminum non-rusting grille
Multi-position pivoting mounting bracket included
Gold plated 14awg binding posts
Includes seismic anchor and safety cable
Also available in 25/70 volt (IO-41W-70)
Sold as pairs
Master carton 2 pairs
1 year warranty



Specifications:

Diameter Woofer 4" (101.6mm) polypropylene
Diameter Tweeter 1" (25.4mm) silk dome
Power Handling 100 watts (peak) 50 watts RMS
Impedance 8 ohms (nominal)
Frequency Response 100Hz - 22kHz (± 10 dB)
Dispersion 95 °
Sensitivity 94dB (1W 1M) Average
Grille material Aluminum
Color White

Included:

Pivoting powder coated steel mounting brackets x 2
Seismic anchors x 2
Aircraft quality safety cable x 2

Dimensions:

Dimensions Overall
Height 9.5" (241.3mm)
Width 6.25" (158.75mm)
Depth 7" (177.8mm) including bracket
Shipping Weight 9.25lbs (4.2kg) per pair

