

#### Features:

Screw-less white Decora cover plate  
 150 watts x 2 power handling  
 12 step attenuation and absolute off  
 Smooth action decora slider  
 8 ohm and 4 ohm operation  
 Impedance match 16 speaker pairs (8ohms)  
 & 32 speaker pairs (4ohms)  
 Heavy duty removable terminal block connectors

#### Includes:

White single gang screw-less decora plate  
 Includes additional almond slider parts  
 Black parts kit available VC-150-BLK  
 3 year warranty



#### Specifications:

**Power Input** 150 Watts x 2 peak  
**Speaker Impedance** 4 – 16 ohms  
 (single or multiple speakers)  
**Mounting Depth** 2- 7/8" (73.02mm)  
**Width Cover Plate** 2-13/16" (71mm)  
**Height Cover Plate** 4-9/16" (116mm)  
**Frequency Response** 20Hz - 20kHz (±3dB)  
**Slider Type** 12 position  
**Attenuation** 12 steps + absolute off  
**Complete Off** Yes  
**Connectors** Dual 4 pin removable terminal block  
 max 14awg wire  
**Mounting Screws** 2 nickel Phillips  
**Master Carton** 24pcs  
**Shipping Weight** 1.25 lbs (0.567kg) each

The VC-150 Kit Includes White & Almond Parts



High Power Handling Transformers &  
 Removable Terminal Block Connectors