

#### Features:

Dual UHF wireless microphone system  
True Dual Diversity operation  
Long range (dropout free) reception  
Includes 2 x professional metal hand held mics  
Infrared microphone auto sync function  
Excellent feedback rejection  
Cardioid pickup pattern (HH mic)

Integrated ON/OFF switches  
3 Pin balanced XLR outputs &  
1/4" unbalanced output  
Receiver with all metal construction  
Dual VFD displays  
Includes 3 x 3' XLR cable  
Includes 4 x 1.5V AA batteries  
Includes rack mounting kit  
Includes aluminum carry case



#### Specifications:

##### Receiver:

Carrier wave freq range - UHF 600-870MHz  
Working freq range – UHF 668-692MHz  
Oscillation Mode – Phase-lock loop controlled  
True Dual Diversity send/receive  
Sensitivity – 105dB @ sinad= 12dB  
S/N ratio – 105dB  
THD - <0.5% @ 1kHz  
Image rejection – 85dB  
Spurious rejection – 75dB  
Frequency response – 40Hz-18kHz  
Working distance 200ft approx (line of sight)  
AF Output impedance – 2.2k ohms  
Max output level – 0-400mv bal / 0-200mv unbal  
Display type – VFD  
Power supply – 800mA 12-18V DC Included

##### Hand-held Transmitter:

Capsule Type – Moving coil dynamic (HH)  
Pickup pattern- Cardioid (HH)  
Frequency Response – 40Hz- 18kHz  
Sensitivity - (-74dB +/- 3dB)  
ON/OFF switch – Yes  
Power – 30mW



Spurious Emission <40dB (with carrier)

Display – LED

Battery voltage 1.5V x 2 AA rechargeable or regular

Battery life- 8 hours approx

##### Dimensions: (W x D x H) Receiver

W= 16.5"/420mm x

D= 8.7"/220mm

H=1.75"/44mm

Shipping Weight 15 lbs (6.8kg)