



Your Best Protection
Against Robbery

Visit us online at
www.gardall.com

Larger/Improved • Lower Cost • Quality Construction



In floor safes are designed to be buried in the floor and concealed by a dust cover under a rug or carpet. Installation should be done by a professional safe dealer.

Standard Features

- UL listed, S&G Group II combination lock
- Hard plate between the lock and dial ring.
- Full length locking bar hinge side of door.
- Independent relocking device to deter forced entry.
- Door frame is reinforced on bolt side.
- Coil spring assist on all doors for ease of opening and closing.
- Dust cover included.
- "B" rate burglary construction.
- 5 active 3/4" bolts on Models 1307, 1311 and 3600..

Square Tube Safe with Liftout Head

Model	Outside Dimensions			Inside Dimensions			Inside Cubic Inches	Approx. Wt. (lbs.)	Door Size
	H	W	D	H	W	D			
G500	8"	8"	11¼"	7⅝"	7⅝"	9"	523	42	7½"x7½"x1/2"
G700	8"	8"	15¼"	7⅝"	7⅝"	13"	755	51	7½"x7½"x1/2"

Commercial In-Floor Safes

Model	Outside Dimensions			Inside Dimensions			Inside Cubic Inches	Approx. Wt. (lbs.)	Door Size
	H	W	D	H	W	D			
B1307*	14¾"	12⅞"	12¼"	13¾"	12½"	8"	1375	100	12"x12"x1/2"
B1311*	14¾"	12⅞"	17¼"	13¾"	12½"	13"	2234	117	12"x12"x1/2"
G3600*	23½"	12½"	17¼"	22¾"	12"	13½"	3686	150	12"x12"x1/2"

Standard color: Gray. All specifications are subject to change without notice. *5 active locking bolts.