



One-Hour Gardall Safes...  
Premium Quality You Can Trust

Visit us online at  
[www.gardall.com](http://www.gardall.com)



Gardall's FB series safes are the next higher level of protection after our U.L. two-hour series safes. They have easily passed both the U.L. Fire and U.L.-R.S.C. tests.

### Fire/Burglary Safe Standard Features

- Heavy duty construction 4" thick door, 3" thick body
- Composite construction door & body
- Independent glass re-locking system
- 3 spoke chrome plated vault handle
- 1 Hour U.L. 350°F Fire Label
- U.L. RSC Burglary Label
- Center bolt down for ease of installation (hardware included)
- 1½" chrome plated locking bolts
- Attractive two tone paint for increased durability
- UL listed, S&G Group II combination lock
- **Gardall Lifetime Replacement Warranty** (see inside front cover)

### Lock Options

- U.L. electronic or key-op lock

Model	Outside Dimensions			Inside Dimensions			Cubic Inches	Approx. Weight (lbs.)	Shelves
	H	W	D	H	W	D			
FB1212	17¾"	17¾"	20½"	12"	12"	12¾"	1836	205	1
FB2013	27"	20"	20½"	20½"	13¾"	12½"	3558	313	2
FB2714	33½"	20"	22¾"	27½"	14¾"	14¾"	5982	412	2

Add 2" to outside depth for dial and handle.