



**Your Best Protection
Against Robbery**

Visit us online at



Gardall Firelined Gun Safes

GF5517

Single Layer of Fire Protection

- 3-way locking bolts - 5 active 1" bolts
- 3 wheel lock with spyproof dial
- 3 spoke handle
- 4 anchoring holes in bottom
- 11 gun capacity
- Powder coated paint
- Safe fits in a standard closet
- Fire tested at 1200°F for 30 minutes
- Premium quality door organizer
- Add 2" to depth for handle

BGF6024/6030/6040

Double Layer of Fire Protection

- 3-way locking bolts - 7 active 1½" bolts
- U.L. Group II lock with spyproof dial
- 2 layers 1/2" U.L. rated fire board insulation
- 5 spoke handle
- 4 anchoring holes in bottom
- Capacity: BGF6024: 16 gun slots
BGF6030: 22 gun slots
BGF6040: 39 gun slots
- U.L. Approved Intumescent door seal expands to 7X original size
- Fire tested at 1400°F for 60 minutes
- U.L. RSC Burglary Label
- 3 dead bolts on hinge side
- Premium quality door organizer

Model	Outside Dimensions			Inside Dimensions			Approx. Weight (lbs.)
	H	W	D	H	W	D	
GF5517	55¼"	17¾"	16"	53"	16"	11½"	265
BGF6024	59½"	24"	22"	55"	21"	16"	520
BGF6030	59½"	30"	26"	55"	26¾"	20"	650
BGF6040	59½"	40"	26"	55"	37¼"	20"	805

Powder Coated Matte Finish: Black. 4 Anchoring Holes with Hardware included.

LaGard Group II combination lock standard. S&G Type I Electronic Lock available as option.