



**Your Best Protection
Against Robbery**

Visit us online at
www.gardall.com



Keep excess till cash locked away and out of sight to prevent loss from pilferage.

Under Counter Depository Safes – 1/2" Plate Steel Door, 1/4" Body

Model	Outside Dimensions			Inside Dimensions			Weight (lbs.)
	H	W	D	H	W	D	
DS86-G-K	8"	6"	12"	7½"	5½"	11"	34
DS86-G-C	8"	6"	12"	7½"	5½"	11"	34
TC1206-G-K	12"	6½"	8"	9¼"	6"	7"	35
TC1206-G-C	12"	6½"	8"	9¼"	6"	7"	35
DS1210-G-K	12"	8"	10"	10¼"	7½"	9"	47
DS1210-G-C	12"	8"	10"	10¼"	7½"	9"	47

Anchoring holes in bottom for easy installation



Compact Utility Safes

Designed for use in walls, basements, car trunks, and RV's. Solid steel plate with insurance "B" rated construction. This safe also features a U.L. listed Group II combination lock. Door will interchange with many other Gardall Safes. 1/2" pre-drilled mounting holes in base.

Standard Features

- 1/2" plate steel door
- Independent relock on lock
- Group II electronic lock (optional)
- UL listed, S&G Group II combination lock
- 4 anchoring holes in bottom

Model	Outside Dimensions			Inside Dimensions			Inside Cubic Inches	Approx. Weight (lbs.)
	H	W	D	H	W	D		
H2-G-C	11¼"	11½"	12¾"	10½"	11"	10¾"	1184	70

Add 1½" to outside depth for dial and handle.